



PART NUMBER	A MAX	B MAX	DIMENSIONS		D DIA +.004 -.002	COMMENT	RELEASE	WT-LB
			SIZE CLASS 2A	PITCH DIA				
10-130506-8	.938	.775	6-32 UNC	.1177-.1141	.156	22588-65	32508-233	
-10	.963	.775						
-12		.837						
-14		.963						
-16		1.087						
-18	1.094	1.150						
-20		1.399	8-32 UNC	.1437-.1399	.180			
-22		1.399						
-24	1.110	1.587						
-28	1.110	1.587						
-32	1.436	2.181	2500-20 UNC	.2175-.2127	.209			
-36		2.306						
-40		2.556						

REL	32508-233	WAS	DATE	D'MAN	
1	33390-2	REDIM CLAMPING EARS	12-4-57	Fabala	
2	33787-17	CHG PICT TO SHOW INTERNAL TOOTH LOCK WASHER	1-30-58	Walker	
A1	48531 -16	STANDARD PRACTICE	11-1-67	Cable	
A2	49524 -603	ADD & REL -XX8	2-18-69	HANNI	
A3	49525 -454	ADD & REL -XX0, -XX6, -XX7, -XX9, FIN; REV THD DATA & NOTE 1	4-16-69	HNDSON	
B	81130	(CLD) ADDED & RELEASE -XX11 FINISH	12-21-99	JED	



10-130506

2. TO COMPLETE ASSEMBLY NUMBER, ADD APPLICABLE
THIRD DIGIT SUFFIX NUMBER FOR DESIRED FINISH:

CHROMATE TREAT.....SUFFIX-XX0
BRIGHT CADMIUM PLATE.....SUFFIX-XX1
BLACK ANODIZE.....SUFFIX-XX2
CADMIUM PLATE, OLIVE DRAB.....SUFFIX-XX3
GREY ANODIZE.....SUFFIX-XX4
TIN ZINC PLATE.....SUFFIX-XX6
NICKEL BASE, CADMIUM PLATE.....SUFFIX-XX7
BRIGHT NICKEL PLATE.....SUFFIX-XX8
OLIVE DRAB, CAD PLATE, NICKEL BASE.....SUFFIX-XX9
OLIVE-GREEN ZINC ALLOY PLATE.....SUFFIX-XX11

RELEASE	COMMENT
32508-233	22588-65
49524-454	
49524-454	
49524-603	
49524-454	

1. FOR QUANTITIES & PART NUMBERS OF THE COMPONENTS
FOR THE DESIRED UNIT, SEE SEPARATE PARTS LIST,

NOTES:

1. PART NUMBERS AND QUANTITIES OF DETAIL
PARTS ARE LISTED ON PARTS LIST (IMPORT)

NOTES: REF SYMBOL

USE OF THIS DOCUMENT IS UNLIMITED. DOCUMENTS
REFERENCED HEREON CONTAIN LIMITED RIGHTS DATA.

MATERIAL SPEC.		PROCESS SPEC.		SCINTILLA DIVISION BENDIX AVIATION CORPORATION SIDNEY, N. Y., U.S.A.				TOLERANCES UNLESS OTHERWISE SPECIFIED	
HEAT TREAT SPEC.		FINISH SPEC.		NAME SLEEVE ASSEMBLY AND INSTALLATION, CABLE CLAMP, ELECTRICAL CONNECTOR				FRACTIONS ± ~ DECIMALS ± .010 ANGLES ± ~	
C.R. SEE ABOVE				D'MAN CHECKER MAT. STDS. CH. D'MAN APPROVED SCALE				CONCENTRICITY, TIR SURFACE ROUGHNESS MICRO-IN RMS MAX.	
				1-25-57 5-24-57 5-25-57 5-31-57 7-8-57				NEXT ASSEMBLY 10-129108/50 2 OTHERS	
								SUPERSEDES AND IS NOT INTERCHANGEABLE	
								SUPERSEDED BY 10-130506	
								REF. TAB. CODE 77820	