

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



UL Recognized type 1 SPD and IEC type 2 surge protection plug with a gas discharge tube and thermal disconnect for use with VAL-US base elements, mechanical and visual fault warning

Product Description

Surge protective device replacement plug

Your advantages

- Plugs can be checked with CHECKMASTER
- Thermal disconnect device for each individual plug
- Pluggable
- Mechanical coding of all slots
- Consists of base element and plug
- Optical, mechanical status indication for the individual arresters

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Commercial Data

Item number	2910342
Packing unit	1 pc
Sales Key	C06
Product Key	CL1321
Catalog Page	Page 93 (C-4-2019)
GTIN	4055626444840
Weight per Piece (including packing)	42.5 g
Weight per Piece (excluding packing)	40 g
Customs tariff number	85363030
Country of origin	DE

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Technical Data

Notes

General	Used in:
---------	----------

Product properties

IEC test classification	II
	T2
EN type	T2
Type	Male
Product type	Replacement plug
Number of positions	1
Surge protection fault message	optical

Insulation characteristics

Overvoltage category	III
Pollution degree	2


Electrical properties

Nominal frequency f_N	50 Hz (60 Hz)
-------------------------	---------------

Connection data

Connection method	VALVETRAB plug-in system
-------------------	--------------------------

Dimensions

Dimensional drawing	
Width	17.5 mm
Width	17.5 mm
Height	52.4 mm
Height	52.4 mm
Depth	55.3 mm
Depth	55.3 mm
Horizontal pitch	1 Div.

Material specifications

Color	jet black RAL 9005
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6/PBT

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Material group	I
Housing material	PA 6.6
	PBT

Protective circuit

Mode of protection	N-PE
Direction of action	N-PE
Nominal voltage U_N	277/480 V AC (TN-S)
	277/480 V AC (TT)
Nominal frequency f_N	50 Hz (60 Hz)
Maximum continuous voltage U_C	305 V AC
Residual current I_{PE}	$\leq 5 \mu A$
Standby power consumption P_C	$\leq 1.5 \text{ mVA}$
Nominal discharge current I_n (8/20) μs	20 kA
Maximum discharge current I_{max} (8/20) μs	40 kA
Follow current interrupt rating I_{fi}	100 A (260 V)
Voltage protection level U_p	$\leq 1.5 \text{ kV}$
Residual voltage U_{res}	$\leq 0.4 \text{ kV}$ (at I_n)
	$\leq 0.25 \text{ kV}$ (at 10 kA)
	$\leq 0.15 \text{ kV}$ (at 5 kA)
	$\leq 0.1 \text{ kV}$ (at 3 kA)
Front of wave sparkover voltage at 6 kV (1.2/50) μs	$\leq 1.5 \text{ kV}$
TOV behavior at U_T	1200 V AC (200 ms / withstand mode)
Response time t_A	$\leq 100 \text{ ns}$

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	$\leq 2000 \text{ m}$ (amsl (above mean sea level))
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x $\pm X$, $\pm Y$, $\pm Z$)
Vibration (operation)	5g (10 ... 500 Hz / 2.5 h / X, Y, Z)

Approval data

UL specifications

UL type	type 1
Maximum Surge Current per Phase	40 kA
Mode of protection	N-G
Nominal voltage	277 V AC
Power distribution system	Single phase
Nominal frequency	50/60 Hz

Type 1 surge protection plug - GDT-US-NG/40-P

2910342

<https://www.phoenixcontact.com/us/products/2910342>



SPD Type	1CA
----------	-----

Standards and regulations

Standards/specifications	IEC 61643-11
Standards/specifications	EN 61643-11

Mounting

Mounting type	on base element
---------------	-----------------


Type 1 surge protection plug - GDT-US-NG/40-P

2910342

<https://www.phoenixcontact.com/us/products/2910342>



Drawings



Circuit diagram



Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Approvals



cUL Recognized
Approval ID: FILE E 330181



UL Recognized
Approval ID: FILE E 330181

cULus Recognized

Type 1 surge protection plug - GDT-US-NG/40-P

2910342

<https://www.phoenixcontact.com/us/products/2910342>



Classifications

ECLASS

ECLASS-9.0	27130890
ECLASS-10.0.1	27130890
ECLASS-11.0	27130890

ETIM

ETIM 8.0	EC002496
----------	----------

UNSPSC

UNSPSC 21.0	39121600
-------------	----------

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Accessories

Type 1 surge protection device

Type 1 surge protection device - VAL-US-120/40/1+1-FM - 2910349

<https://www.phoenixcontact.com/us/products/2910349>



Surge protective device, two channel with remote indicator contact for 120 V AC, 2-wire plus ground.

Type 1 surge protection device

Type 1 surge protection device - VAL-US-120/40/2+1-FM - 2910352

<https://www.phoenixcontact.com/us/products/2910352>



Surge protective device, three channel with remote indicator contact for 120/240 V split phase AC, 3-wire plus ground.

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Type 1 surge protection device

Type 1 surge protection device - VAL-US-120/40/3+1-FM - 2910354

<https://www.phoenixcontact.com/us/products/2910354>



Surge protective device, four channel with remote indicator contact for 120/208 V Wye three phase AC, 4-wire plus ground.

Type 1 surge protection device

Type 1 surge protection device - VAL-US-240/40/1+1-FM - 2910362

<https://www.phoenixcontact.com/us/products/2910362>



Surge protective device, two channel with remote indicator contact for 240 V AC, 2-wire plus ground.

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Type 1 surge protection device

Type 1 surge protection device - VAL-US-240/40/2+1-FM - 2910365

<https://www.phoenixcontact.com/us/products/2910365>



Surge protective device, three channel with remote indicator contact for 240/480 V split phase AC, 3-wire plus ground.

Type 1 surge protection device

Type 1 surge protection device - VAL-US-240/40/3+1-FM - 2910367

<https://www.phoenixcontact.com/us/products/2910367>



Surge protective device, four channel with remote indicator contact for 240/415 V AC, 4-wire plus ground.

Type 1 surge protection plug - GDT-US-NG/40-P



2910342

<https://www.phoenixcontact.com/us/products/2910342>

Type 1 surge protection device

Type 1 surge protection device - VAL-US-240HLD/40/3+1-FM - 2910371

<https://www.phoenixcontact.com/us/products/2910371>



Surge protective device, four channel with remote indicator contact for 240 V AC high-leg DELTA.

Type 1 surge protection device

Type 1 surge protection device - VAL-US-277/40/1+1-FM - 2910373

<https://www.phoenixcontact.com/us/products/2910373>



Surge protective device, two channel with remote indicator contact for 277 V AC, 2-wire plus ground.

Type 1 surge protection plug - GDT-US-NG/40-P

2910342

<https://www.phoenixcontact.com/us/products/2910342>



Type 1 surge protection device

Type 1 surge protection device - VAL-US-277/40/3+1-FM - 2910374

<https://www.phoenixcontact.com/us/products/2910374>



Surge protective device, four channel with remote indicator contact for 277/480 V AC, 4-wire plus ground.

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com