

K10P-11D15-120 Product Details



Industrial Relays (General Purpose)

Converted to EU RoHS but not ELV Compliant (Statement of Compliance)

Product Highlights:

- Relay Type = Miniature
- Relay Style = General
- K10 Series
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 15 A

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

K10P-11D15-120

(5-1393144-6)

TE Internal Number: 5-1393144-6

Active

[View 3D PDF](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [K10 15 Amp General Purpose Miniature Relay](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version 0303)
- [3D Model](#) (IGES, Version 0303)
- [3D Model](#) (STEP, Version 0303)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Additional Product Images:

- [Schematic](#)
- [PCB Layout](#)
- [Wiring Diagram](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Termination Type](#) = .187 x .020 Quick Connect Terminals

Electrical Characteristics:

- [Contact Current Rating \(A\)](#) = 15
- [Coil Resistance \(\$\Omega\$ \)](#) = 11000
- [Actuating System](#) = DC
- [Coil Power, Nominal \(W\)](#) = 0.90
- [Input Voltage \(VDC\)](#) = 120

Body Related Features:

- [Series](#) = K10
- Polarized = No

Contact Related Features:

- Relay Type = Miniature
- [Mounting Options](#) = Socket
- [Enclosure Type](#) = Enclosed
- FCC Part 68 Isolation = No
- [Contact Base Material](#) = Silver Cadmium Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 28.20 x 21.80 x 34.90 [1.111 x .858 x 1.375]
- Wiring Diagram = 2 Form C
- Approved Standards = UL Recognized, CSA Certified

Configuration Related Features:

- Relay Style = General
- [Contact Arrangement](#) = 2 Form C, DPDT, 2 C/O
- [Coil Magnetic System](#) = Monostable
- [Coil Suppression Diode](#) = Without
- [Coil Selection Criteria](#) = Nominal Voltage
- Coil Latching = Without
- Status Indicator = None

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS/Not ELV Compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Converted to comply with RoHS not ELV directives
- Coil Insulation Classification = Class B

Other:

- Brand = Potter & Brumfield

BOOKMARK

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)

Sign up for our eNewsletter

Enter your email address

Follow us on:

