





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/7/05	
A		ADDED DIM.	4/25/13	



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 2 Amps max

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 15
A = .079 [2.00] x No. of Positions + .075 [1.90]
B = .079 [2.00] x No. of Spaces

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE
.079 [2.00] SHROUDED HEADER
STRAIGHT, PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES							
.X	± .10	ØXX	± .10	DRAWN	SS	4/7/05	SIZE
.XX	± .020	ØXXX	± .015	CHECKED			X
.XXX	± .015	ØXXX	± .010	APPROVED			REF:
APPROVALS	DATE						SCALE: NTS
							SHEET 1 OF 1

6

5

4

3

2

1

6

5

4

3

2

1

D

D

C

C

B

B

A

A