

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)

11_BNC-50-2-14/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
BNC	plug	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium / Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data	
Weight	0.0098 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-65 °C ... 165 °C

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)
11_BNC-50-2-14/133_N

Ordering Information Table		
Item number	Item description	Packaging type
22641683	11_BNC-50-2-14/133_NE	Single
22649839	11_BNC-50-2-14/133_NH	Bulk 100 pcs

Suitable cables	
Cable group	U4 - 2 mm / 50 Ohm
Suitable cables	G_02232_D
	K_02252_D
	ENVIROFLEX_316_D

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3706 / Date of publication: 17.01.2024 / uncontrolled copy