

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

---



Complete package consisting of ELR H51-IESSC-24DC500AC-9 and EM-RD-ADAPTER for mounting on 35 mm DIN rails.

---

## Your advantages

- 22.5 mm wide
- Safety level according to IEC 61508-1: SIL 3, ISO 13849: PL e
- Reduction in wiring
- Long service life
- Space saving
- Adjustable current for bimetal function
- Low-wear switching

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

## Commercial Data

Item number	2902954
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	C05
Product Key	CK7454
Catalog Page	Page 37 (C-5-2019)
GTIN	4046356701877
Weight per Piece (including packing)	487 g
Weight per Piece (excluding packing)	350 g
Customs tariff number	85371098
Country of origin	DE

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

## Technical Data

### Product properties

Product type	Hybrid motor starter
Set consists of	2902745 ELR H51-ISSC-24DC500AC-9
	2902747 EM RD-ADAPTER
	2903384 FUSE-10X38-20A-GR
Operating mode	100% operating factor

### Electrical properties

Number of phases	3
Motor starter type	Reversing starter
Maximum power dissipation for nominal condition	11 W
Switching frequency	≤ 2 Hz (Load-dependent)
Maximum power dissipation	7 W
Minimum power dissipation	0.88 W
Coordination type	2

### Supply

Rated control circuit supply voltage $U_S$	24 V DC
Control supply voltage range	19.2 V DC ... 30 V DC
Rated control supply current $I_S$	40 mA
Protective circuit	Surge protection
	Reverse polarity protection; Parallel polarity protection diode

### Insulation characteristics

Rated insulation voltage	500 V
Rated surge voltage	6 kV
Overvoltage category	III
Degree of pollution	2
Insulation characteristics between the control input and control supply voltage, and auxiliary circuit to the main circuit	Safe isolation (IEC 60947-1) at operating voltage ≤ 300 V AC
	Safe isolation (EN 50178) at operating voltage ≤ 300 V AC
	Basic isolation (IEC 60947-1) at operating voltage 300 ... 500 V AC
	Safe isolation (EN 50178) at operating voltage 300 ... 500 V AC
Isolation characteristics between the control input and control supply voltage to auxiliary circuit	Safe isolation (IEC 60947-1) in the auxiliary circuit ≤ 300 V AC
	Safe isolation (EN 50178) in the auxiliary circuit ≤ 300 V AC

### Emergency tripping

Operate threshold	> 45 A
Response time	< 2 s

### Input data

#### Control

Input name	Control input right/left
------------	--------------------------

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

Rated actuating voltage $U_C$	24 V DC
Triggering voltage range	19.2 V DC ... 30 V DC
Rated actuating current $I_C$	5 mA
Switching threshold	9.6 V ("0" signal)
	19.2 V ("1" signal)
Switching level	< 5 V DC (For EMERGENCY STOP)
Typical turn-off time	< 30 ms

## Output data

### AC output

Rated operating voltage $U_e$	500 V AC
Operating voltage range	42 V AC ... 550 V AC
Mains frequency	50/60 Hz
Load current range	1.5 A ... 9 A (see to derating)
Trigger characteristic in acc. with IEC 60947-4-2	Class 10A
Cooling time	20 min. (for auto reset)
Leakage current	0 mA
Protective circuit	Surge protection; Varistor
	Short-circuit protection; Fuse

### Acknowledge output

Note	Confirmation: floating change-over contact, signal contact
Contact type	1 changeover contact
Switching capacity according to IEC 60947-5-1	3 A (230 V, AC15)
	2 A (24 V, DC13)

## Connection data

### Control circuits

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section AWG	24 ... 14
Torque	0.5 Nm ... 0.6 Nm
	5 lb <sub>f</sub> -in. ... 7 lb <sub>f</sub> -in.

### Control circuits

Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Conductor cross section solid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross section AWG	24 ... 14

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

Torque	0.5 Nm ... 0.6 Nm
	5 lb <sub>F</sub> in. ... 7 lb <sub>F</sub> in.

## LED signaling

Status display	Yellow LED
Operating voltage display	Green LED
Indication	Red LED

## Dimensions

Width	22.5 mm
Height	185 mm
Depth	142.6 mm

## Material specifications

Flammability rating according to UL 94	V0 (Housing)
--	--------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C (observe derating)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

## Approval data

### ATEX

Identification	<input type="checkbox"/> II (2) G [Ex e] [Ex d] [Ex px]
	<input type="checkbox"/> II (2) D [Ex t] [Ex p]
Certificate	PTB 07 ATEX 3145

### ATEX

Certificate	NLDX.E228652
-------------	--------------

### ATEX

Identification	≤ 3
Note	Safe shutdown

### ATEX

Identification	2
Note	Motor protection

### ATEX

Identification	e
Note	Safe shutdown

### ATEX

Identification	3
----------------	---

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

Note	Safe shutdown
------	---------------

## UL data

SCCR	100 kA (480 V AC (fuse: 30 A class CC/30 A class J (high fault)))
	5 kA (480 V AC (fuse: 20 A RK5 (standard fault)))
FLA	6.5 A (480 V AC)
Group installation	20 A (class RK5, SCCR 5kA, #24 - 14 AWG max. solid and stranded)
	30 A (class CC or J, SCCR 100kA, #24 - 14 AWG max, solid and stranded)
Category code	NLDX / NRNT

## Standards and regulations

### Standards/regulations

Standards/regulations	IEC 60947-1
	EN 60947-4-2
	IEC 61508
	ISO 13849

## Mounting

Mounting type	DIN rail mounting
Assembly instructions	alignable, for spacing see derating
Mounting position	vertical (horizontal DIN rail, motor output below)

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

## Classifications

### ECLASS

ECLASS-9.0	27370905
ECLASS-10.0.1	27370905
ECLASS-11.0	27370905

### ETIM

ETIM 7.0	EC001037
----------	----------

### UNSPSC

UNSPSC 21.0	25173902
-------------	----------

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"



# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

## Accessories

### Fuse

Fuse - FUSE-10X38-30A-MR - 2903119

<https://www.phoenixcontact.com/us/products/2903119>



Fuse, number: 10 Pcs., fuse type: Fuse (CC), nominal current: 30 A, tripping characteristic: fast-blow (F)

---

### Fuse

Fuse - FUSE-10X38-20A-GR - 2903384

<https://www.phoenixcontact.com/us/products/2903384>



Fuse, number: 10 Pcs., fuse type: Fuse (CC), nominal current: 20 A, tripping characteristic: super-fast blow (gR)

# Hybrid motor starter - ELR H51-9-DIN-RAIL-SET



2902954

<https://www.phoenixcontact.com/us/products/2902954>

## Fuse

Fuse - FUSE-10X38-16A-GR - 2903126

<https://www.phoenixcontact.com/us/products/2903126>



Fuse, number: 10 Pcs., fuse type: Fuse (CC), nominal current: 16 A, tripping characteristic: super-fast blow (gR)

---

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)