


**Part Number :** [734154330](#)

**Product Description :** MCX Jack, Right-Angle, PCB Receptacle, Surface Mount, Die Cast Housing with Brass Insert, Nickel (Ni) Plated Outer Contact, Tri-Metal Plated Housing, Tray, 75 Ohms

**Series Number :** 73366

**Status :** Active

**Product Category :** RF / Coaxial Connectors



---

## Documents and Resources

### Drawings

[734154330 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	RF / Coaxial Connectors
Series	73366
Description	MCX Jack, Right-Angle, PCB Receptacle, Surface Mount, Die Cast Housing with Brass Insert, Nickel (Ni) Plated Outer Contact, Tri-Metal Plated Housing, Tray, 75 Ohms
Application	RF
Product Name	MCX
Style	PCB
Type	Microminiature
UPC	822348057788

### Electrical

Frequency	6 GHz
Impedance	75Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

### Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A

Net Weight	1.559/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Surface Mount
PCB Thickness - Recommended	N/A
Reverse Polar	No
Wire/Cable Type	N/A

### Solder Process Data

Max-Duration	5
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	265

---

This document was generated on Feb 05, 2026