


## 250 & 500W Single Output Power Supplies

### Features

- ◆ High Efficiency, up to 93%
- ◆ 1.6" high (For 1U racking)
- ◆ Wide Range AC Input
- ◆ 250W Convection Cooled
- ◆ Five year warranty



### Key Market Segments & Applications



GWS500 Shown



Specifications			
Model		GWS250	GWS500
AC Input Voltage (300VAC for 5s)	VAC	85 - 264VAC	
Input Frequency	Hz	47 - 63Hz	
DC Input Voltage	VDC	120 - 373VDC*	
Inrush Current (cold start)	A	20A at 115VAC, 40A at 230VAC	
Power Factor (1)	-	Meets EN61000-3-2 (Typical PF 0.98/0.95)	
Input Current (115/230VAC)	A	3.0 / 1.4	5.5 / 2.7
Temperature Coefficient	°C	<0.02%/°C (0 - 50°C)	
Overcurrent Protection	-	>105% of nominal or >101% of peak. 12V hiccup style, 24V-48V Constant current style	
Overvoltage Protection (2)	V	12V: 13.8 - 16.2V 24V: 30.3 - 35.5V, 36V: 41.4 - 48.6V, 48V: 60 - 69.6V	
Overtemperature Protection (2)	-	Yes	
Hold Up Time (115 / 230V input)	ms	16ms	
Leakage Current (230VAC 60Hz)	mA	<0.75mA	
Remote Sense	-	No	Yes
Remote On/Off	-	Active Low	
Standby Input Power Draw	W	<0.5W	
5V Standby (always on)	-	5V 0.3A	
DC Good	-	DC Good, open collector signal, High on Fail	
LED Indicator	-	Green LED = On	
Output Remote Programming	-	See installation manual for details	
Operating Temperature	°C	-25 to +70°C. Derate linearly to 50% load from +50 to +70°C	-25 <sup>(3)</sup> to +70°C. Derate linearly to 50% load from +50 to +70°C
Storage Temperature	°C	-30 to +85°C	
Operating Humidity	-	30 - 90% RH (non condensing)	
Storage Humidity	-	10 - 95% RH (non condensing)	
Cooling	-	Convection	Internal fan
Withstand Voltage	-	Input to Ground 1.5kVAC, Input to Output 3kVAC, Output to Ground 500VAC <sup>(4)</sup> for 1 min.	
Isolation Resistance	-	>100M at 25°C & 70%RH, Output to Ground 500VDC	
Vibration (non operating)	-	10 - 55Hz: 19.6m/s <sup>2</sup> constant sweep 1 min X, Y, Z for 1 hour	
Shock	-	< 196.1 m/s <sup>2</sup> (20G)	
Immunity	-	IEC61000-4-2 (lv 2, 3), -3 (lv3), -4 (lv 3), -5 (lv 3), -6 (lv 3), -8 (lv 4), -11	
Safety Agency Approvals	-	UL60950-1, CSA C22.2 No 60950-1-07 (cUL), EN60950-1 2nd Edition, IEC60950-1, CE Mark	
Conducted & Radiated EMI	-	EN55022-B, FCC-B	
Weight (Typ)	g	850	1020
Size (LxWxH)	in	7.8 x 4.1 x 1.61"	8.6 x 4.1 x 1.61"
Warranty	yrs	Five Years	

(1) 115 / 230VAC input

(2) Recycle AC, or use remote on/off to reset

(3) Guaranteed start up at -40°C

(4) 500VDC for GWS500

\*Safety certified for AC input only

