

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	20[mm]
Max. Air Flow:	20.5[CFM]
Max. Air Flow:	0.58[m3 per min]
Max. Static Pressure:	0.2[In H2O]
Max. Static Pressure:	49.1[Pa]
Fan Speed:	4400[RPM]
Noise:	30.5[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	9[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.07[A]
Input Power:	1.7[W]
Mass:	56[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	Active