
Part Number : 731000103
Product Description : SMB Jack, Right-Angle, PCB Receptacle, Through Hole, Brass Body, Gold (Au) Plated, 80 Pieces Per Tray, 50 Ohms
Series Number : 73404
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

731000103_sd.pdf

895420089-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-73598-0099-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:1bfc1b78-6af0-4e60-92cb-18747643e488
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73404
Description	SMB Jack, Right-Angle, PCB Receptacle, Through Hole, Brass Body, Gold (Au) Plated, 80 Pieces Per Tray, 50 Ohms
Application	RF
Product Name	SMB
Style	PCB
Type	Subminiature
UPC	800753686359

Electrical

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 335 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	3.695/g
Orientation	Right Angle

Downloaded from Arrow.com.

Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	Through Hole
PCB Thickness - Recommended	2.40mm
Reverse Polar	No
Wire/Cable Type	N/A

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	2
Max-Temp	260

Downloaded from Arrow.com.