MOSFET – Power, Single N-Channel


40 V, 370 A, 0.67 mΩ

NVMFS5C404NL


$V_{(BR)DSS}$	$R_{DS(ON)}$ MAX	I_D MAX
40 V	0.67 mΩ @ 10 V	370 A
	1.0 mΩ @ 4.5 V	

Features


- Small Footprint (5x6 mm) for Compact Design
- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Q_G and Capacitance to Minimize Driver Losses
- NVMFS5C404NLWF – Wettable Flank Option for Enhanced Optical Inspection
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant



N−CHANNEL MOSFET



DFN5
CASE 506EZ



DFNW5
CASE 507BA

MAXIMUM RATINGS (T_J = 25 °C unless otherwise noted)

Symbol	Parameter			Value	Unit
V_{DSS}	Drain-to-Source Voltage			40	V
V_{GS}	Gate-to-Source Voltage			±20	V
I_D	Continuous Drain Current $R_{\theta JC}$ (Notes 1, 3)	Steady State	T_C = 25 °C	370	A
			T_C = 100 °C	260	
P_D	Power Dissipation $R_{\theta JC}$ (Note 1)		T_C = 25 °C	200	W
			T_C = 100 °C	100	
I_D	Continuous Drain Current $R_{\theta JA}$ (Notes 1, 2, 3)	Steady State	T_A = 25 °C	52	A
			T_A = 100 °C	37	
P_D	Power Dissipation $R_{\theta JA}$ (Notes 1 & 2)		T_A = 25 °C	3.9	W
			T_A = 100 °C	1.9	
I_{DM}	Pulsed Drain Current	T_A = 25 °C, t_p = 10 μs		900	A
T_J, T_{stg}	Operating Junction and Storage Temperature			−55 to + 175	°C
I_S	Source Current (Body Diode)			191	A
E_{AS}	Single Pulse Drain-to-Source Avalanche Energy ($I_{L(pk)}$ = 38 A)			907	mJ
T_L	Lead Temperature for Soldering Purposes (1/8″ from case for 10 s)			260	°C


Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Junction-to-Case – Steady State	0.75	°C/W
$R_{\theta JA}$	Junction-to-Ambient – Steady State (Note 2)	39	

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.
2. Surface−mounted on FR4 board using a 650 mm^2, 2 oz. Cu pad.
3. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

MARKING DIAGRAM



XXXXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

See detailed ordering, marking and shipping information in the package dimensions section on page 5 of this data sheet.

NOTE: Some of the devices on this data sheet have been **DISCONTINUED**. Please refer to the table on page 5.

© Semiconductor Components Industries, LLC, 2016

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25 °C unless otherwise specified)

Symbol	Parameter	Test Condition		Min	Typ	Max	Unit
OFF CHARACTERISTICS							
$V_{(BR)DSS}$	Drain−to−Source Breakdown Voltage	V_{GS} = 0 V, I_D = 250 μA		40			V
$V_{(BR)DSS}/T_J$	Drain−to−Source Breakdown Voltage Temperature Coefficient				21.6		mV/°C
I_{DSS}	Zero Gate Voltage Drain Current	V_{GS} = 0 V, V_{DS} = 40 V	T_J = 25 °C			10	μA
			T_J = 125°C			250	
I_{GSS}	Gate−to−Source Leakage Current	V_{DS} = 0 V, V_{GS} = 20 V				100	nA
ON CHARACTERISTICS (Note 4)							
$V_{GS(TH)}$	Gate Threshold Voltage	V_{GS} = V_{DS}, I_D = 250 μA		1.2		2.0	V
$V_{GS(TH)}/T_J$	Threshold Temperature Coefficient				−6.2		mV/°C
$R_{DS(on)}$	Drain−to−Source On Resistance	V_{GS} = 10 V	I_D = 50 A		0.52	0.67	mΩ
		V_{GS} = 4.5 V	I_D = 50 A		0.75	1.0	
g_{FS}	Forward Transconductance	V_{DS} =15 V, I_D = 50 A			270		S
CHARGES, CAPACITANCES & GATE RESISTANCE							
C_{ISS}	Input Capacitance	V_{GS} = 0 V, f = 1 MHz, V_{DS} = 25 V			12168		pF
C_{OSS}	Output Capacitance				4538		
C_{RSS}	Reverse Transfer Capacitance				79.8		
$Q_{G(TOT)}$	Total Gate Charge	V_{GS} = 4.5 V, V_{DS} = 20 V; I_D = 50 A			81		nC
$Q_{G(TOT)}$	Total Gate Charge	V_{GS} = 10 V, V_{DS} = 20 V; I_D = 50 A			181		
$Q_{G(TH)}$	Threshold Gate Charge	V_{GS} = 4.5 V, V_{DS} = 20 V; I_D = 50 A			8.5		
Q_{GS}	Gate−to−Source Charge				27.8		
Q_{GD}	Gate−to−Drain Charge				23.8		
V_{GP}	Plateau Voltage				2.7		V
SWITCHING CHARACTERISTICS (Note 5)							
$t_{d(ON)}$	Turn−On Delay Time	V_{GS} = 4.5 V, V_{DS} = 20 V, I_D = 50 A, R_G = 1.0 Ω			24		ns
t_r	Rise Time				135		
$t_{d(OFF)}$	Turn−Off Delay Time				87		
t_f	Fall Time				157		
DRAIN−SOURCE DIODE CHARACTERISTICS							
V_{SD}	Forward Diode Voltage	V_{GS} = 0 V, I_S = 50 A	T_J = 25 °C		0.7	1.2	V
			T_J = 125 °C		0.61		
t_{RR}	Reverse Recovery Time	V_{GS} = 0 V, dIS/dt = 100 A/μs, I_S = 50 A			97.4		ns
t_a	Charge Time				46.5		
t_b	Discharge Time				50.9		
Q_{RR}	Reverse Recovery Charge				190		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

4. Pulse Test: pulse width ≤ 300 μs, duty cycle ≤ 2%.
5. Switching characteristics are independent of operating junction temperatures.

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-Resistance vs. Gate−to−Source Voltage




Figure 4. On-Resistance vs. Drain Current and Gate Voltage




Figure 5. On-Resistance Variation with Temperature




Figure 6. Drain-to-Source Leakage Current vs. Voltage

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (continued)




Figure 7. Capacitance Variation




Figure 8. Gate-to-Source and Drain-to-Source Voltage vs. Total Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage vs. Current




Figure 11. Safe Operating Area




Figure 12. I_{PEAK} vs. Time in Avalanche

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS (continued)




Figure 13. Thermal Characteristics

DEVICE ORDERING INFORMATION

Device	Case	Marking	Package	Shipping†
NVMFS5C404NLWFT1G	507BA	404LWF	DFNW5 (Pb-Free, Wettable Flanks)	1500 / Tape & Reel
NVMFS5C404NLAFT1G	506EZ	5C404L	DFN5 (Pb-Free)	1500 / Tape & Reel
NVMFS5C404NLWFAFT1G	507BA	404LWF	DFNW5 (Pb-Free, Wettable Flanks)	1500 / Tape & Reel
NVMFS5C404NLAFT3G	506EZ	5C404L	DFN5 (Pb-Free)	5000 / Tape & Reel
NVMFS5C404NLWFAFT3G	507BA	404LWF	DFNW5 (Pb-Free, Wettable Flanks)	5000 / Tape & Reel
NVMFS5C404NLWFET3G	507BA	404LWF	DFN5 (Pb-Free, Wettable Flanks)	5000 / Tape & Reel
NVMFS5C404NLET1G	506EZ	5C404L	DFN5 (Pb-Free)	1500 / Tape & Reel
NVMFS5C404NLWFET1G	507BA	404LWF	DFNW5 (Pb-Free, Wettable Flanks)	1500 / Tape & Reel

DISCONTINUED (Note 6)

NVMFS5C404NLT1G	506EZ	5C404L	DFN5 (Pb-Free)	1500 / Tape & Reel
NVMFS5C404NLT3G	506EZ	5C404L	DFN5 (Pb-Free)	5000 / Tape & Reel
NVMFS5C404NLWFT3G	507BA	404LWF	DFN5 (Pb-Free, Wettable Flanks)	5000 / Tape & Reel

† For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

6. **DISCONTINUED:** These devices are not available. Please contact your **onsemi** representative for information. The most current information on these devices may be available on www.onsemi.com.

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.


REVISION HISTORY

Revision	Description of Changes	Date
13	Revision to add NVMFS5C404NLET1G and NVMFS5C404NLWFET1G Device	12/18/2025

This document has undergone updates prior to the inclusion of this revision history table. The changes tracked here only reflect updates made on the noted approval dates.

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.




SCALE 2:1


DFN−5, 4.90x5.90x1.00, 1.27P
CASE 506EZ
ISSUE C

DATE 18 JUN 2026


NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2018.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.




TOP VIEW



DETAIL "A"
SCALED 2:1




SIDE VIEW



BOTTOM VIEW


MILLIMETERS			
DIM	MIN	NOM	MAX
A	0.90	1.00	1.10
A1	0.00	−−−	0.05
b	0.33	0.41	0.51
c	0.23	0.28	0.33
D	5.00	5.15	5.30
D1	4.70	4.90	5.10
D2	3.80	4.00	4.20
E	6.00	6.15	6.30
E1	5.70	5.90	6.10
E2	3.45	3.80	3.85
e	1.27 BSC		
G	0.51	0.575	0.71
k	1.10	1.20	1.40
L	0.51	0.575	0.71
L1	0.125 REF		
M	3.00	3.40	3.80
θ	0°	−−−	12°
TOLERANCE FORM & POSITION			
bbb	0.10		
ccc	0.10		
ddd	0.05		
eee	0.10		

GENERIC MARKING DIAGRAM*



XXXXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, "G" or microdot " ▪", may or may not be present. Some products may not follow the Generic Marking.




RECOMMENDED MOUNTING FOOTPRINT

*For additional information on our Pb−Free strategy and soldering details, please download the onsemi Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

DOCUMENT NUMBER:	**98AON24855H**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**DFN−5, 4.90x5.90x1.00, 1.27P**	**PAGE 1 OF 1**


onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.


Downloaded from Arrow.com.





DFNW5 4.90x5.90x1.00, 1.27P
CASE 507BA
ISSUE C


DATE 19 SEP 2024












NOTES:

1. DIMENSIONING AND TOLERANCING CONFORM TO ASME Y14.5M−2018.
2. ALL DIMENSIONS ARE IN MILLIMETERS.
3. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
4. THIS PACKAGE CONTAINS WETTABLE FLANK DESIGN FEATURES TO AID IN FILLET FORMATION ON THE LEADS DURING MOUNTING.


DIM	MILLIMETERS		
	MIN	NOM	MAX
A	0.90	1.00	1.10
A1	0.00	---	0.05
b	0.33	0.41	0.51
c	0.23	0.28	0.33
D	5.00	5.15	5.30
D1	4.70	4.90	5.10
D2	3.80	4.00	4.20
E	6.00	6.15	6.30
E1	5.70	5.90	6.10
E2	3.45	3.65	3.85
E3	3.00	3.40	3.80
e	1.27 BSC		
k	1.20	1.35	1.50
L	0.51	0.57	0.71
L2	0.15 REF.		
θ	0°	6°	12°



RECOMMENDED MOUNTING FOOTPRINT*

*FOR ADDITIONAL INFORMATION ON OUR Pb−FREE STRATEGY AND SOLDERING DETAILS, PLEASE DOWNLOAD THE ONSEMI SOLDERING AND MOUNTING TECHNIQUES REFERENCE MANUAL, SOLDERRM/D.

GENERIC MARKING DIAGRAM*



XXXXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, "G" or microdot " ▪", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	**98AON26450H**	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	**DFNW5 4.90x5.90x1.00, 1.27P**	**PAGE 1 OF 1**

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.