



CONNECTORS

HEADERS & RECEPTACLES



Active

TE CONNECTIVITY (TE)
EP2.5 HDR 7P VERT W/O BOSS, TAPING, BLACK

Economy Power | Economy Power 2.5

3-2299683-7
TE Internal Number: 3-2299683-7

EU RoHS Compliant
EU ELV Compliant

Connector System Wire-to-Board
Termination Method to Wire/Cable Solder
Sealable No
PCB Mounting Orientation Vertical
Circuit Application Power

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

HEADER ASSEMBLY, VERTICAL ECONOMY POWER, 2.5mm CENTERLINE TAPING VERSION
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Application Specification

Economy Power (EP) 2.5 Contacts; Plug And Receptacle Housings; And Vertical And Right-Angle Headers

PDF

English

Product Specification

EP 2.5 Connector System

PDF

English

Agency Approvals

UL Report

ECONOMY POWER 2.5 CONNECTOR REPORT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Board

Sealable No

PCB Mounting Orientation Vertical

Connector & Contact Terminates To Printed Circuit Board

Product Type Connector

Connector Type Header

Connector Style Plug

Glow Wire Rating Standard Part - Not Glow Wire

Configuration Features

Number of Positions 7

Number of Rows 1

Tail Orientation Inline

Selectively Loaded No

Backwall/Post Interruptions Without

Electrical Characteristics

Operating Voltage (VAC) 250

Body Features

Color Black
Header Type Shrouded

Contact Features

Contact Mating Area Plating Material Tin
Contact Mating Area Plating Thickness 2.03 μm [80 μin]
Contact Current Rating (Max) (A) 4.2
Contact Style Straight
Contact Base Material Brass
Contact Layout Inline
Contact Termination Area Plating Material Tin
Contact Termination Area Plating Thickness (μin) 80
Tail Plating Thickness 2.032 μm [80 μin]
Contact Transmits (Typical) Power, Signal (Data)
Tail Plating Material Tin
Contact Design Round Post
Contact Shape Round
Contact Type Pin

Termination Features

Termination Method to Wire/Cable Solder
Termination Method to PC Board Through Hole - Solder

Mechanical Attachment

PCB Mounting Style Through Hole
PCB Mount Alignment Without
Mating Retention With
PCB Mount Retention Without
Mating Alignment With
Mating Retention Type Latch
Mating Alignment Type Polarization
Contact Retention Without

Housing Features

Centerline (Pitch) 2.5 mm [.098 in]
Housing Material PBT
Housing Color Black

Dimensions

Height 8.8 mm [.346 in]
Tail Length 3.4 mm [.134 in]
Width 6.4 mm [.252 in]
PCB Thickness (Recommended) 1.6 mm [.063 in]
Length 20 mm [.79 in]
Mating Post Length 3.6 mm [.142 in]

Usage Conditions

Operating Temperature Range -55 – 105 °C [131 – 221 °F]

Operation/Application

Circuit Application Power

For Use With Connector/Cable Assembly

Packaging Features

Packaging Method Tape

Packaging Quantity 450

Statement of Compliance

Statement of Compliance

PDF