



PRODUCT NUMBER	PITCH
T9xx21x000J0G	5.08 mm




N = Number of poles
 Dim L = N x 5.08
 Dim P = (N-1) x 5.08

Poles	Tolerance
2-6p	±0.15
7-12p	±0.30
13-18p	±0.35
19-24p	±0.40

PART NO.: T9 xx 21 x 0 00J0 G

End stackable	No. of poles	Body Color	RoHS compliant (lead<4%)
0	2	Black (RAL9005)	In copper Alloy
02	2 poles	Red (RAL3001/D)	
03	3 poles	Orange(RAL2011/P)	
...	...	4 Yellow(RAL1018/A)	
...	...	5 Green(RAL6018/T)	
24	24 poles	6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	



RECOMMENDED P.C.B LAYOUT
 TOP VIEW

Material:

- Item ① Terminal body(metal housing): Brass(CuZn),Tin plated
- Item ② Terminal screw: Steel Zinc plating "-" slot type
- Item ③ Wire guard: Stainless steel
- Item ④ Insulator (housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 15A
- Wire range:
- Solid wire(AWG): 14-24
- Stranded wire(AWG): 14-24
- Toque(Lb-In): 3.2
- Screw: M2.6
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C ±5°C/5 Sec
- Safety Approval: 

mat'l. code				surface	tolerance	projection	product family		
litr ecn no dr date				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK		
				tolerances unless otherwise specified		MM	title		
				angles	X.±0.5		TERMINAL BLOCK		
				flat	X.X±0.3		WIRE PROTECTOR,90D WIRE INLET		
				X*±1°	X.XX±0.1	scale	dwg no		
				dr	EVIN ZHONG	040114	sheet 1 of 1		
				enrg	EVIN ZHONG	040114	size		
				chr	HANKE FENG	040114	T9xx21x000J0G		
				appd	SHI JUN	040114	A4		
							type		
							CUSTOMER Drawing		
sheet index	revision	A							
	sheet	1							