


ITEM NO.	PART NUMBER	DESCRIPTION	QTY.	COMPONENT NOTES
1	50-00112	Connector, dc plug, 3.5x1.35xL18.5 mm, brass nickel plated	1	
2	30-00003	Wire, 2C BC, 24 AWG, UL2468, 300V, 80C, 3.6 mm, VW-1, PVC	1	
3	24-00050	Overmold, PVC	1	black



Ratings
Maximum operating voltage: 48 V
Maximum operating current: 4.5 A
Hi-Pot test: 600 Vac, 0.5 mA, 1 second

Operating Temperature Range
-25 ~ 80 °C, relative humidity of 85% or less

Wiring Diagram	
50-00112	wire color
center	black with stripe
sleeve	black

Revision:	Date:	Description:	Prepared:	Notes:	<div>TENSILITY</div> <div> tel 1.541.323.3228 800 877.670.7118 fax 1.541.323.4202 web tensility.com </div> <div> <div>Size: A</div> <div>Part number: 053-0192R (CA-2193)</div> </div> <div> <div>Scale: 1:1</div> <div> </div> <div>Sheet 1 of 1</div> </div>		
A	1/19/2009	Re-issue CUI spec as Tensility	CR <small>Digitally signed by CR Date: 2026.01.29 13:57:36 -08'00'</small>	RoHS and REACH compliant			
A1	1/19/2011	Added overmold dimensions, and updated description	Verified: KM <small>Digitally signed by KM Date: 2026.02.27 12:09:07 -08'00'</small>	Function test: no open, no short circuit, no intermittent			
A2	8/31/2011	Updated description, connector, and wire information	Dimensions are in millimeters. Tolerances: X: ± 0.5 mm X.X: ± 0.3 mm X.XX: ± 0.05 mm	Description: Cable, 1830 mm, 3.5x1.35x9.5 mm, 50-00112 dc plug to stripped tinned, 24 AWG, 30-00003 wire			
A3	10/9/2013	Changed connector to 50-00112					
A4	12/9/2016	Updated overmold dimension					