



Part Number : [307005100](#)

Product Description : 2.54mm Pitch, H-DAC 64 High Density Automotive Header, Dual Row, Right-Angle, 10 Circuits, Polarization Option 1, Gray, Tray

Series Number : 30700

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[307005100 sd.pdf](#)

[PK-30907-260-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)


[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[PS-30700-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	30700
Description	2.54mm Pitch, H-DAC 64 High Density Automotive Header, Dual Row, Right-Angle, 10 Circuits, Polarization Option 1, Gray, Tray
Application	Automotive, Power, Wire-to-Board
Comments	Polarization Option 1
Component Type	PCB Header
Product Name	H-DAC 64
UPC	800754874687

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	500V DC

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10

Color - Resin	Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	Modified Polystyrene
Net Weight	4.777/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm
PC Tail Length	3.69mm
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-40° to +100°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	40
Lead-Free Process Capability	SMC&WAVE
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
2.54mm Pitch, 0.64mm Width H-DAC 64 High Density Automotive Connectors, Dual Row, Female Harness Assembly, 10 Circuits, Polarization Option 1, Gray	<u>307001100</u>

This document was generated on Apr 29, 2026