



LDC	D157			REVISIONS				
AJ	16	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
		✓	✓		F	REDWN, REV & ADD 3--9 PER AJ-4562	8-8-91	BAS



VIEW X



VIEW Y
SAME AS VIEW X
EXCEPT AS SHOWN

- ① BERYLLIUM COPPER PER QQ-C-530
- ② GOLD PLATE PER MIL-G-45204
1.27 μ m [.000050] MINIMUM THICK
- ③ GOLD PLATE PER MIL-G-45204
0.76 μ m [.000030] MINIMUM THICK
- ④ GOLD PLATE PER MIL-G-45204
2.54 μ m [.000100] MINIMUM THICK
- ⑤ SILVER PLATE PER QQ-S-385
2.54 μ m [.000100] MINIMUM THICK

Y	4	10.39 [.409]	5.08 [.200]	0.79 [.031]	3-331368-9
Y	5	10.39 [.409]	5.08 [.200]	0.79 [.031]	3-331368-8
X	3	10.39 [.409]	5.84 [.230]	0.36 [.014]	2-331368-4
Y	3	10.39 [.409]	5.08 [.200]	0.46 [.031]	2-331368-3
X	2	10.39 [.409]	5.08 [.200]	0.46 [.018]	2-331368-2
X	3	10.69 [.421]	5.08 [.200]	0.89 [.035]	2-331368-1
X	3	11.73 [.462]	5.08 [.200]	0.61 [.024]	1-331368-6
X	3	10.39 [.409]	5.08 [.200]	0.46 [.018]	1-331368-4
X	3	10.39 [.409]	5.08 [.200]	0.61 [.024]	1-331368-2
Y	2	10.39 [.409]	5.08 [.200]	0.79 [.031]	331368

VIEW	FINISH	C	B	A	PART NUMBER
------	--------	---	---	---	-------------

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON :
2 PLC DEC $\pm$ 0.20 [0.008]
3 PLC DEC $\pm$ -
ANGLES $\pm$ -

MATERIAL

**FINISH**

SEE TABLE

DR 2-8-91
B. SCOTT

CHK 3-20-91
J. LIPPERT

APPD 4-3-91
M. PHILLIPS

APPD 4-3-91
J. LIPPERT

PRODUCT SPEC	
--------------	--

APPLICATION SPEC

100

WEIGHT

AMP

AMP Incorporated
Harrisburg, PA 17105-3608

NAME

CONTACT, RECEPTACLE,
DUAL CRIMP, SERIES BNC

	SIZE
--	------

CAGE CODE	
-----------	--

15

00779

DRAWING NO

SCAL	
------	--

E 12:1

	SHEET
--	-------

1 OF 1