

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Box mounting bases B16, with single locking latch, material: Die-cast aluminum, salt water resistant, cable outlets: 2, lateral, 2x M32, height: 68 mm, cable gland: none, Standard

Your advantages

- good shielding in the event of electromagnetic interference

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Commercial Data

Item number	1412862
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	B10
Product Key	BF7APB
Catalog Page	Page 619 (C-2-2019)
GTIN	4055626061115
Weight per Piece (including packing)	292.8 g
Weight per Piece (excluding packing)	291.3 g
Customs tariff number	85389099
Country of origin	CN

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Technical Data


Notes

General	For contact inserts HC-B16, BB32, D40, DD72, HS6, HV6, M, K
---------	---

Product properties

Type	B16
Product type	Housing with locking latch
Application	Standard
No. of cable outlets	2
Type of the screw connection	2x M32
Housing type	Box mounting bases
Locking type	with single locking latch
Cable outlet	lateral
Pg screw connection	none

Dimensions

Dimensional drawing	
Width	57 mm
Height	68 mm
Length	117.5 mm
Hole diameter	5.5 mm

Material specifications

Color	gray aluminum
Flammability rating according to UL 94	V0 (Interlock)
Sealing material	NBR, conductive (profile gasket)
Housing surface material	uncoated
Locking latch material	PA
Impact strength	IK08
Housing material	Die-cast aluminum, salt water resistant

Ambient conditions

Degree of protection	IP66
	IP67
Degree of protection	4 (UL 50e)
	4X (UL 50e)
	12 (UL 50e)
Impact strength	IK08

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Ambient temperature (operation)	-40 °C ... 125 °C
---------------------------------	-------------------

Mechanical properties

Mechanical data

Type of the screw connection	2x M32
Locking type	Latch

Mounting

Assembly instructions	One opening is sealed with a plastic filler plug and can be opened using a screwdriver.
-----------------------	---

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL


1412862

<https://www.phoenixcontact.com/us/products/1412862>



Drawings

Dimensional drawing



Dimensional drawing


Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL





1412862

<https://www.phoenixcontact.com/us/products/1412862>


Approvals

**DNV**
Approval ID: TAE000037S

**cUL Recognized**
Approval ID: E255026

**UL Recognized**
Approval ID: E255026

**EAC**
Approval ID: RU C-DE.AI30.B.01102

**EAC**
Approval ID: RU C-DE.BL08.B.00511

cULus Recognized

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Classifications

ECLASS

ECLASS-9.0	27440202
ECLASS-10.0.1	27440202
ECLASS-11.0	27440202

ETIM

ETIM 8.0	EC000437
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Accessories

Cable gland

Cable gland - G-INS-M32-M68N-NNES-S - 1411166

<https://www.phoenixcontact.com/us/products/1411166>



Cable gland, cable gland material: Nickel-plated brass, external cable diameter 15 mm ... 21 mm, shielding: no, connecting thread: M32 x 1.5, color: silver, with O-ring

Screw connection

Screw connection - WP-G HF IP66 M32 BK - 3240900

<https://www.phoenixcontact.com/us/products/3240900>



Cable gland, metric thread, IP66 protection, straight

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Cable gland

Cable gland - G-INSEC-M32-M68N-NCRS-S - 1411191

<https://www.phoenixcontact.com/us/products/1411191>



Cable gland, cable gland material: Nickel-plated brass, external cable diameter 14 mm ... 21 mm, shielding: yes, connecting thread: M32 x 1.5, color: silver, with O-ring

Screw connection

Screw connection - WP-G HF IP69K M32 BK - 3240886

<https://www.phoenixcontact.com/us/products/3240886>



Cable gland, metric thread, IP68/69k protection, straight

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Profile gasket

Profile gasket - HC-B16-SP-CBK - 1411480

<https://www.phoenixcontact.com/us/products/1411480>

Profile gasket for HEAVYCON EVO supporting base element type B16, conductive



Screw connection

Screw connection - WP-GA HF IP66 M32 BK - 3240928

<https://www.phoenixcontact.com/us/products/3240928>

Cable gland, metric thread, IP66 protection, angled



Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Housing brackets

Housing brackets - HC-STA-B16-SL-PLBK - 1412284

<https://www.phoenixcontact.com/us/products/1412284>



Single locking latch for B16 housing, HC-EVO....AL and HC-STA....AL

Screw connection

Screw connection - WP-GA HF IP69K M32 BK - 3240914

<https://www.phoenixcontact.com/us/products/3240914>



Cable gland, metric thread, IP68/69k protection, angled

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Protective cover

Protective cover - HC-B16-BC-HI-PLBK - 1407694

<https://www.phoenixcontact.com/us/products/1407694>

Protective cover B16, for single locking latch, protective cover material: PC, height: 19 mm, seal: no



Screw connection

Screw connection - WP-GR HF IP66 M32 BK - 3240956

<https://www.phoenixcontact.com/us/products/3240956>

Cable gland, metric thread, IP66 protection, with strain relief



Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Screw connection

Screw connection - WP-GR HF IP69K M32 BK - 3240942

<https://www.phoenixcontact.com/us/products/3240942>



Cable gland, metric thread, IP68/69k protection, with strain relief

Screw connection

Screw connection - WP-G PP HF M32 - 3241000

<https://www.phoenixcontact.com/us/products/3241000>



Cable gland made from PP with metric thread, IP65 protection

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Screw connection

Screw connection - WP-GT PP HF M32 - 3241014

<https://www.phoenixcontact.com/us/products/3241014>



Cable gland made from PP with metric thread, rotatable, IP54 protection

Screw connection

Screw connection - WP-G BRASS IP40 M32 - 3241049

<https://www.phoenixcontact.com/us/products/3241049>



Cable gland made from brass with metric thread, IP40 protection

Housing - HC-STA-B16-SLWS-2SSM32-ELC-AL



1412862

<https://www.phoenixcontact.com/us/products/1412862>

Screw connection

Screw connection - WP-GT BRASS M32 - 3241035

<https://www.phoenixcontact.com/us/products/3241035>

Cable gland made from brass with metric thread, rotatable, IP40 protection



Screw connection

Screw connection - WP-G BRASS IP65 M32 - 3241063

<https://www.phoenixcontact.com/us/products/3241063>

Cable gland made from brass with metric thread, IP65 protection



Phoenix Contact 2022 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com