

Han-Yellock 30 carrier hood button plain



Image is for illustration purposes only. Please refer to product description.

Part number	11 12 300 0100
Specification	Han-Yellock 30 carrier hood button plain
HARTING eCatalogue	https://harting.com/11123000100

Identification

Category	Hoods / Housings
Series of hoods/housings	Han-Yellock®
Type of hood/housing	Carrier hood
Description of hood/housing	Plain push button

Version

Size	Han-Yellock® 30
Locking type	Push button
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Un-/locking temperature	-10 ... +85 °C
Mating cycles	≥500
Degree of protection acc. to IEC 60529	IP65 IP67

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Passivated
Colour (hood/housing)	Metallic
Material (seal)	NBR



Pushing Performance
 Since 1945

Material properties

Material (locking)	Polyamide (PA) Stainless steel
Colour (locking)	Melon yellow
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	216 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140109834
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466