

Subminiature Fuse, 8.5 mm, Time-Lag T, 250 VAC, 100 A



Subminiature fuse 8.5 mm, time-lag T,
250 VAC
Short terminal
PCB

Subminiature fuse time-lag T
from front side
Terminal long

IEC 60127-3 · 250 VAC · Time-Lag T

See below:

[Approvals and Compliances](#)**Description**

- Directly solderable on printed circuit boards
- High breaking capacity

Applications

- Primary Protection on PCB
- Power Supply Adapter for e.g. laptops
- SMPS (Switching Mode Power Supply) for TV's and DVD's

References

Last order date: 30.04.2026

Last delivery date: 31.07.2026

Weblinks

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated Voltage	250 VAC	Soldering Methods	Wave
Rated current	0.8 - 10 A		Soldering Profile
Breaking Capacity	100 A	Solderability	235 °C / 2 sec acc. to IEC 60068-2-20, Test Ta
Characteristic	Time-Lag T	Resistance to Soldering Heat	260 °C / 10sec acc. to IEC 60068-2-20, Test Tb
Mounting	PCB,THT	Case Resistance	acc. to EIA/IS-722, Test 4.7 >100 MΩ (between leads and body)
Admissible Ambient Temp.	-40 °C to 85 °C	Flammability	UL 94V-0 (acc. to EIA/IS-722, Test 4.12)
Climatic Category	40/085/21 acc. to IEC 60068-1	Resistance to Vibration	acc. to IEC 60068-2-6, test Fc
Material: Housing	Thermoplastic, UL 94V-0	Moisture Sensitivity Level	MIL-STD-202, Method 106 (50 cycles in a temp./mister chamber)
Material: Terminals	Tin-Plated Copper	Operational Time	1000h @ 0.60 x In @ 70 °C (acc. to EIA/IS-722, Test 4.4.1)
Unit Weight	0.78 g	Load Humidity Test	MIL-STD-202, Method 103 0.1 x In @ 0.85 r.H. @ 85 °C
Storage Conditions	0 °C to 40 °C, max. 70% r.h.	Mechanical Shock	MIL-STD-202, Method 213 Condition A
Product Marking	 Type, Rated current, Rated Voltage, Characteristic, Certification marks	Resistance to Solvents	MIL-STD-202, Method 215
		Terminal Strength	Tensile load min. 9 N (acc. to EIA/IS-722, Test 4.5.5)

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type: MXT 250

Approval Logo	Certificates	Certification Body	Description
	VDE Approvals	VDE	VDE Certificate Number: 40008838
	VDE Approvals	VDE	VDE Certificate Number: 40024477
	UL Approvals	UL	UL File Number: E41599
	UL Approvals	UL	UR File Number: E41599
	CCC Approvals	CCC	CCC Certificate Number: 2020970207000094
	KTL Approvals	KTL	Korea Testing Laboratory
	METI Approvals	METI	Japan Electrical Safety and Environment technology Laboratories

Product standards

Product standards that are referenced

Organization	Design	Standard	Description
	Designed according to	IEC 60127-3/4	Miniature fuses - Part 3: Miniature fuse-links
	Designed according to	UL 248-14	Low voltage fuses - Part 14: Supplemental fuses
	Designed according to	CSA22.2 No. 248.14	Low-Voltage Fuses - Part 14: Supplemental Fuses

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
	Suitable for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements


Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimension [mm]

8.5 mm




Drilling diagram

Pre-Arcing Time

Rated Current I _n	1.0 x I _n min.	1.5 x I _n min.	2.0 x I _n max.	2.1 x I _n max.	2.75 x I _n min.	2.75 x I _n max.	4.0 x I _n min.	4.0 x I _n max.	10.0 x I _n min.	10.0 x I _n max.
0.8 A - 6.3 A	-	60 min	-	120 s	400 ms	10 s	150 ms	3 s	20 ms	150 ms
8 A - 10 A	4 h	-	60 s	-	-	-	-	-	-	-

Time-Current-Curves



Variants

Rated Current [A]	Rated Voltage [VAC]	Breaking Capacity	Voltage Drop 1.0 I _n max. [mV]	Voltage Drop 1.0 I _n typ. [mV]	Power Dissipation 1.5 I _n max. [mW]	Melting I ² t 10.0 I _n typ. [A ² s]	DVE	VDE	UL	US C	UL US	PS E	CCC	JET	S	L	T	Order Number
0.8	250	1)	160	128	430	1.5	•					•	•	•	•			0034.6914
1	250	1)	140	130	500	4.4	•					•	•	•	•			0034.6915
1.25	250	1)	130	120	600	6.3	•					•	•	•	•			0034.6916
1.6	250	1)	120	110	730	10	•					•	•	•	•			0034.6917
2	250	1)	100	85	870	16	•					•	•	•	•			0034.6918

Rated Current [A]	Rated Voltage [VAC]	Breaking Capacity	Voltage Drop 1.0 I _n max. [mV]	Voltage Drop 1.0 I _n typ. [mV]	Power Dissi- pation 1.5 I _n max. [mW]	Melting I ² t 10.0 I _n typ. [A²s]									S	L	T	Order Number	
2.5	250	1)	100	85	1000	32	●				●	●	●	●	●				0034.6919
3.15	250	1)	100	75	1200	57	●				●	●	●	●	●				0034.6920
4	250	1)	100	75	1400	77	●				●	●	●	●	●				0034.6921
5	250	1)	-	70	-	155					●	●				●			0034.6922
6.3	250	1)	-	60	-	262		●			●	●	●			●			0034.6923
8	250	2)	-	62	-	397			●							●			0034.6924
10	250	2)	-	62	-	440			●							●			0034.6925
0.8	250	1)	160	128	430	1.5	●				●		●	●		●			0034.6944
1	250	1)	140	130	500	4.4	●				●	●	●	●		●			0034.6945
1.25	250	1)	130	120	600	6.3	●				●	●	●	●		●			0034.6946
1.6	250	1)	120	110	730	10	●				●	●	●	●		●			0034.6947
2	250	1)	100	85	870	16	●				●	●	●	●		●			0034.6948
2.5	250	1)	100	85	1000	32	●				●	●	●	●		●			0034.6949
3.15	250	1)	100	75	1200	57	●				●	●	●	●		●			0034.6950
4	250	1)	100	75	1400	77	●				●	●	●	●		●			0034.6951
5	250	1)	-	70	-	155					●	●				●			0034.6952
6.3	250	1)	-	60	-	262		●			●	●	●			●			0034.6953
8	250	2)	-	62	-	397			●							●			0034.6954
10	250	2)	-	62	-	440			●							●			0034.6955
0.8	250	1)	160	128	430	1.5	●				●		●	●		●			0034.6974
1	250	1)	140	130	500	4.4	●				●	●	●	●		●			0034.6975
1.25	250	1)	130	120	600	6.3	●				●	●	●	●		●			0034.6976
1.6	250	1)	120	110	730	10	●				●	●	●	●		●			0034.6977
2	250	1)	100	85	870	16	●				●	●	●	●		●			0034.6978
2.5	250	1)	100	85	1000	32	●				●	●	●	●		●			0034.6979
3.15	250	1)	100	75	1200	57	●				●	●	●	●		●			0034.6980
4	250	1)	100	75	1400	77	●				●	●	●	●		●			0034.6981
5	250	1)	-	70	-	155					●	●				●			0034.6982
6.3	250	1)	-	60	-	262		●			●	●	●			●			0034.6983
8	250	2)	-	62	-	397			●							●			0034.6984
10	250	2)	-	62	-	440			●							●			0034.6985

Availability for all products can be searched real-time: <https://www.schurter.com/en/info-center/support-tools/stock-check-distributors>

- 1) 100 A @ 250 VAC, cos φ = 1.0
2) 100 A @ 250 VAC, cos φ = 0.95 - 1.0

Packaging Unit acc. IEC 60286-2	S =	100 pcs in ESD-plastic bag
	L =	100 St. (Bulk)
	T =	750 pcs. in tape [P = P0: 12.7; P1: 3.81; H1: 26.45] on reel [A: 360; W3: 40; W4: 52; C: 30.5]