



CDBUR0230**I_o = 200 mA****V_R = 30 Volts****RoHS Device****Features**

- Designed for mounting on small surface.
- Extremely thin/leadless package.
- Low drop-down voltage.
- Majority carrier conduction.

Mechanical data

- Case: 0603/SOD-523F standard package, molded plastic.
- Terminals: Gold plated, solderable per MIL-STD-750, method 2026.
- Polarity: Indicated by cathode band.
- Mounting position: Any
- Weight: 0.003 gram(approx.).

**Maximum Rating (at T_A=25°C unless otherwise noted)**

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Repetitive peak reverse voltage		V _{RRM}			35	V
Reverse voltage		V _R			30	V
Average forward current		I _o			200	mA
Forward current,surge peak	8.3 ms single half sine-wave superimposed on rate load(JEDEC method)	I _{FSM}		3000		mA
Power Dissipation		P _D			150	mW
Snction temperature		T _{STG}	-40		+125	°C
Junction temperature		T _j			+125	°C

Electrical Characteristics (at T_A=25°C unless otherwise noted)

Parameter	Conditions	Symbol	Min	Typ	Max	Unit
Forward voltage	I _F = 200 mA DC	V _F			0.50	V
Reverse current	V _R = 30V	I _R			30	uA
Capacitance between terimnals	F = 1 MHZ and 10 VDC reverse voltage	C _T		9		pF

RATING AND CHARACTERISTIC CURVES (CDBUR0230)

Fig. 1 - Forward characteristics




Fig. 2 - Reverse characteristics




Fig.3 - Capacitance between terminals characteristics




Fig.4 - Current derating curve

