

1840413-8 Product Details

Share

Print

Email



1840413-8

TE Internal Number: 1840413-8

Active

Mag45 - RJ45 with Integrated Magnetics

Always EU RoHS/ELV Compliant (Statement of Compliance)

- Product Highlights:
- Connector
 - 10/100BASE-T Ethernet Application
 - Number of Cores = 4
 - Operating Temperature = 0 - 70 °C
 - Status Indicator = LED
- [View all Features](#)

- Quick Links
- Check Pricing & Availability
 - Search for Tooling
 - Product Feature Selector
 - Contact Us About This Product

Add to My Part List

Request Sample

Find Similar Products

Buy Product

Documentation & Additional Information	
Product Drawings: 1X1 MAG45(TM),MODULAR JACK,326P10 MAGNETIC CIRCUIT,S... (PDF, English) Catalog Pages/Data Sheets: - None Available Product Specifications: - None Available Application Specifications: - None Available Instruction Sheets: - None Available CAD Files: - None Available List all Documents	Related Products: Tooling

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: - Product Type = Connector - Magnetics = Integrated Magnetics - Jack Type = RJ45 - Signal Routing Type = Auto MDI/MDIX - Profile = Standard - PCB Mounting Orientation = Side Entry (Right Angle) Electrical Characteristics: - Turns Ratio = 1:1 - Shielded = Yes Termination Features: - Contact Termination Type = Through Hole - Termination Method = Solder Body Features: - Port Configuration = Single - EMI Fingers -Top and Sides = With - EMI Finger - Bottom = Without - Latch Orientation = Standard - Latch Down - PCB Tail Length (mm [in]) = 3.68 [0.145] Contact Features: - Preloaded = Yes Housing Features: - Connector Style = Jack	Configuration Features: - Number of Cores = 4 - Status Indicator = LED - Jack Configuration = 1 x 1 - Decoupling Capacitor = 2KV - Rear PCB Ground Tab = Without - Signal Lead Quantity = 8 Industry Standards: - RoHS/ELV Compliance = RoHS compliant, ELV compliant - Lead Free Solder Processes = Wave solder capable to 260°C, Wave solder capable to 240°C, Wave solder capable to 265°C - RoHS/ELV Compliance History = Always was RoHS compliant Identification Marking: - Left LED Color (Position #1) = Green - Right LED Color (Position #2) = Yellow Environmental: - Operating Temperature (°C [°F]) = 0 - 70 [32 - 158] Conditions for Usage: - Applies To = Printed Circuit Board - Environmental Conditions = Office / Premises Operation/Application: - Application = 10/100BASE-T Ethernet Other: - PlanarMag = No - Brand = Tyco Electronics

Corporate Information

About TE

Investors

News Room

Supplier Portal

Careers

Terms & Conditions

Privacy Policy

Quick Links

Check Distributor Inventory

Cross Reference Products

Find Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us

Find a Phone Number

Search Knowledge Base

Manage Your Account

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

