

Search...

SPC5643LAMMM1 :Part Detail

General Information	Package Information	Environmental and Compliance Information	Manufacturing Information	Ordering Information
Operating Characteristics				

General Information

Part Number	SPC5643LAMMM1
Description	Freescale 32-bit MCU, Dual Power Arch, 1MB Flash, 120MHz, -40/+125degC, Automotive Qual, MAPBGA257
Product Line	G9V5643A
PTI	JBSL
Material Type	Tested Packaged Device
Life Cycle Description (code) (/webapp/sps/site/eialink.jsp)	PRODUCT RAPID GROWTH
Status	Active
SafeAssure Functional Safety (http://www.nxp.com/about/about-nxp/technology-leadership/safeassure-functional-safety-program:SAFETYPRGRM)	ISO 26262
Application/Qualification Tier (/webapp/sps/site/aqtlink.jsp?type=pop_up)	AUTO; >=10 YEARS APPLICATION LIFE

Package Information

Package Type and Termination Count	MAPBGA257
Package Description and Mechanical Drawing	MAPBGA257 14*14*0.7P0.8
Device Weight(g)	0.40720
Package Length (nominal)(mm)	14.000
Package Width (nominal)(mm)	14.000
Package Thickness (nominal)(mm)	1.510
Maximum Height Above Board(mm)	1.510
Tape & Reel	No

Environmental and Compliance Information

Pb-Free (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=PBFREE_INFO&type=pop_up)	
RoHS Compliant (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_INFO&type=pop_up)	
Halogen Free (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=HALOGEN_FREE_INFO)	Yes
Material Composition Declaration (MCD) (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_MCD&type=pop_up)	Download MCD Report  (/mcds/SPC5643LAMMM1.pdf) Download MCD Report  (/mcds/SPC5643LAMMM1.xls)
RoHS Certificate of Analysis (CoA) (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=ROHS_COA&type=pop_up)	Contact Us (https://nxpcommunity.force.com/community/communityContactSupport)
2nd Level Interconnect (http://www.nxp.com/webapp/sps/utis/showCollateral.jsp?code=PLATING_INDICATOR_INFO)	e2
Moisture Sensitivity Level (MSL)	3
Floor Life	168 HOURS

Peak Package Body Temperature (PPT)(°C)	260
Maximum Time at Peak Temperature (s)	40
Number of Reflow Cycles	3
REACH SVHC	NXP REACH Statement (/files/corporate/doc/support_info/NXP-REACH-STATEMENT.pdf)
UL94 (plastics flammability test)	V0;Burning stops within 10 seconds on a vertical specimen;no drips allowed

Manufacturing Information

Micron Size(μm)	.09
-----------------	-----

Ordering Information

Minimum Package Quantity (MPQ)	760
MPQ Container	BRICK
Exempt from Minimum Delivery Value	Yes
Preferred Order Quantity (POQ)	1520
POQ Container	BOX
Export Control Classification Number (US)	3A991A2
Harmonized Tariff (US) Disclaimer (/webapp/sps/site/harmTariffDisclaim.jsp)	8542.31.0000
CCATS Document	-
ENC Status	-
Other Trade Compliance Documents	-
Budgetary Price excluding tax(US\$) (/webapp/sps/site/bplink.jsp) Change Currency	-
Order	

Operating Characteristics

Sample Exception Availability	N
-------------------------------	---

ABOUT NXP

Investors (<http://investors.nxp.com/phoenix.zhtml?c=209114&p=irol-irhome>)
Partners (<http://www.nxp.com/webapp/connect/memberDirSearch.sp>)
Careers (<http://www.nxp.com/about/careers-at-nxp:CAREERS>)

RESOURCES

Mobile Apps (<http://www.nxp.com/about/nxp-mobile-applications:MOBILE>)
Press, News, Blogs (<http://media.nxp.com>)
Contact Us (<http://www.nxp.com/pages/contact-us:CONTACTUS>)

FOLLOW US

(<https://twitter.com/NXP>) (<http://www.linkedin.com/company/nxp-semiconductors>) (<https://www.facebook.com/NXPsemi>)

(<https://contact.nxp.com/Subscription-Center>)

News 16 Feb 2017
NXP Wins Prestigious Automotive Innovation Award with Radar
Read More (<http://phx.corporate-ir.net/phoenix.zhtml?c=254228&p=irol-newsArticle&cat=news&id=2246510>)

