

Single Supply Dual Operational Amplifiers



SOP-8

DIP-8

Pin assignment:



General Description

Utilizing the circuit designs perfected for recently introduced Quad Operational Amplifiers, these dual operational amplifiers have several distinct advantages over standard operational amplifier types in single supply applications. They can operate at supply voltages as low as 3.0 Volts or as high as 32 Volts with quiescent currents about one fifth of those associated with the LM741 (on a pet amplifier basis). The common mode input range includes the negative supply, thereby eliminating the necessity for external biasing components in many applications. The TS358/TS2904 is equivalent to one half of TS324/TS2902, and output voltage range also includes the negative supply voltage.


Features

- Short circuit protected outputs
- True differential input stage
- Single supply operation: 3V to 32V
- Low input bias currents
- Internally compensated
- Common mode range extends to negative supply
- Single and split supply operation
- Similar performance to the popular MC1558

Ordering Information

Part No.	Package	Packing
TS358CD C3	DIP-8	50pcs / Tube
TS358CS RL	SOP-8	2.5Kpcs / 13" Reel
TS2904CD C3	DIP-8	50pcs / Tube
TS2904CS RL	SOP-8	2.5Kpcs / 13" Reel

Block Diagram



Absolute Maximum Rating

Parameter		Symbol	Limit	Unit	
Supply Voltage	TS358	V _{cc}	+32 or ±16	V	
Supply Voltage	TS2904	vcc vcc	+26 or ±13	V	
Differential Input Voltage	TS358	\/	32	V	
(Split Power Supplies)	TS2904	V _{IDR}	26		
Input Common Mode Voltage Range (note 1)		V _{ICR}	-0.3 to 32	V	
			-0.3 to 26	V	
Input Forward Current (note 2)		I _{IF}	50	mA	
Output Short Circuit Duration		tsc	Continuous		
Operating Junction Temperature Bange	TS358		0 ~ +70	°C	
Operating Junction Temperature Range	TS2904	T _J	-40 ~ +85	C	
Storage Temperature Range		T _{STG}	-65 ~ +150	°C	

Note 1: For supply. Voltages less than 32V/26V for the TS358/TS2904 the absolute maximum input voltage is equal to the supply voltage.

Note 2: This input current will only exist when the voltage is negative at any of the input leads. Normal output states will reestablish when the input voltage returns to a voltage greater than -0.3V.



Single Supply Dual Operational Amplifiers



Electrical Characteristics

(V_{CC} = 5V, Ta=25°C; unless otherwise specified.)

Characteristics	Symbol	TS358		TS2904		Unit		
	Symbol	Min	Тур	Max	Min	Тур	Max	Ullit
Input Offset Voltage								
V_{CC} = 5.0V to 30V, V_{IC} = 0V to Vcc -1.7 V,	Vio		2.0	7.0		2.0	5.0	mV
Vo= 1.4V, R_S = 0Ω	V10			9.0			10	''''
T _{LOW} ≤ Ta ≤T _{HIGH}								
Average Temperature Coefficient of Input	ΔΙίο/ΔΤ		7.0			7.0		uV/°C
Offset Voltage	ДПО/ДТ							uv, 0
Input Offset Current	lio		5.0	50		5.0	50	nA
T _{LOW} ≤ Ta ≤T _{HIGH}	110			150			150	117.
Average Temperature Coefficient of input	ΔΙίο/ΔΤ		10			10		pA/°C
Offset Current	Дпо/Д1							p, (, O
Input Bias Current	l _{IB}		-45	-250		-45	-250	nA
T _{LOW} ≤ Ta ≤T _{HIGH}	чв		-50	-500		-50	-500	117 \
Input Common-Mode Voltage Range)								
V _{CC} = 30 V (Note1)	V _{ICR}	0		28.3	0		24.3	\ \ \
V _{CC} = 30 V, T _{LOW} ≤ Ta ≤T _{HIGH}		0		28	0		24	
Differential Input Voltage Range	V_{IDR}			V _{cc}			V _{cc}	V
Large Signal Open-Loop Voltage Gain								
$R_L = 2.0K$, $V_{CC} = 15V$, For Large V_O Swing,	A _{VOL}	25	100		25	100		V/mV
T _{LOW} ≤ Ta ≤T _{HIGH}		15			15			
Channel Separation			-120			-120		dB
1.0 KHz to 20KHz								
Common Mode Rejection Ratio	CMRR	65	70		50	70		dB
$R_S \le 10 \text{ k}\Omega$								
Power Supply Rejection Ratio	PSRR	65	100		50	100		dB
Output Voltage Range, RL = 2KΩ	V _{OR}	0		3.3	0		3.3	V
Output Voltage High Limit								
$V_{CC} = 30 \text{ V}, R_L = 2 \text{ k}\Omega$	V _{OH}	26			22			V
$V_{CC} = 30 \text{ V}, R_L = 10 \text{ k}\Omega$		27	28		23	24		
Output Voltage Low Limit	V _{OL}		5.0	20		5.0	100	mV
$V_{CC} = 5.0 \text{ V}, R_L = 10 \text{ k}\Omega$								
Output Source Current V _{ID} =+1.0V,V _{CC} =15V	I _{O+}	20	40		20	40		mA
Output Sink Current								
$V_{ID} = -1.0 \text{ V}, V_{CC} = 15 \text{ V}$	l _{O-}	10	20		10	20		mA
$V_{ID} = -1.0 \text{ V}, V_{O} = 200 \text{ mV}$		12	50		12	50		uA
Output Short Circuit to Ground (Note 2)	los		40	60		40	60	mA
Power Supply Current ,			,_			, _		_
$V_{CC} = 30 \text{ VV}_{O} = 0 \text{ V}, R_{L} = \infty$	I _{CC}		1.5	3.0		1.5	3.0	mA
$V_{CC} = 5.0 \text{ V}, V_{O} = 0 \text{ V}, R_{L} = \infty$			0.7	1.2		0.7	1.2	

Notes:

- 1. The input common mode voltage or either input signal voltage should not be allowed to go negative by more than 0.3 V. The upper end of the common mode voltage range is Vcc 17V, but either or both inputs can go to +32V.
- 2. Short circuits from the output to Vcc can cause excessive heating and eventual destruction. Destructive dissipation can recruit from simultaneous shorts on all amplifiers.
- 3. TS358: Tlow=0°C, Thigh=+70°C TS2904: Tlow=-40°C, Thigh=+85°C



Pb RoHS

Single Supply Dual Operational Amplifiers

Electrical Characteristics Curve




Figure 1. Large Signal Voltage Follower Response




Figure 3. Open Loop Frequency




Figure 5. Small-Signal Voltage Follower Pulse Response (Noninverting)




Figure 2. Input Voltage Range




Figure 4. Large Signal Frequency Response




Figure 6. Power Supply Current vs. Supply Voltage



COMPLIANCE

Single Supply Dual Operational Amplifiers

Application Description

The TS358/TS2904 made using two internally compensated, two-stage operational amplifiers. The first stage performs not only the first stage gain function but also performs the level shifting and transconductance reduction functions. By reducing the transconductance, a smaller compensation capacitor (only 5.0pF) can be employed, thus saving chip area. Another feature of this input stage is that the input common mode range can include the negative supply or ground, in single supply operation, without saturating either the input devices or the differential to single-ended converter. The second stage consists of a standard current source load amplifier stage.

Each amplifier is biased from an internal-voltage regulator, and which has a low temperature coefficient thus giving each amplifier good temperature characteristics as well as excellent power supply rejection.




Figure 7. Voltage Reference

Figure 8. Wien Bridge Oscillator




Figure 9. Bi-Quad Filter



Single Supply Dual Operational Amplifiers



Application Description (Continue)




Figure 10. High Impedance Differential Amplifier

Figure 11. Comparator with Hysteresis





Figure 12. Function Generator



For less than 10% error from operational amplifier. $\frac{Q_0 f_0}{BW} < 0.1$

Where fo and BW are expressed in Hz.

If source impedance varies, filter may be preceded with voltage follower buffer to stabilize filter parameters.


Figure 13. Multiple Feedback Bandpass Filter





Single Supply Dual Operational Amplifiers


SOP-8 Mechanical Drawing



001 0211121101011					
DIM	MILLIMETERS		INCHES		
	MIN	MAX	MIN	MAX.	
Α	4.80	5.00	0.189	0.196	
В	3.80	4.00	0.150	0.157	
С	1.35	1.75	0.054	0.068	
D	0.35	0.49	0.014	0.019	
F	0.40	1.25	0.016	0.049	
G	1.27BSC		0.05BSC		
K	0.10	0.25	0.004	0.009	
М	0°	7°	0°	7°	
Р	5.80	6.20	0.229	0.244	
R	0.25	0.50	0.010	0.019	
•		•	•		

SOP-8 DIMENSION

Marking Diagram



Y = Year Code

M = Month Code

(A=Jan, B=Feb, C=Mar, D=Apl, E=May, F=Jun, G=Jul, H=Aug, I=Sep, J=Oct, K=Nov, L=Dec)

L = Lot Code




Downloaded from Arrow.com.






Single Supply Dual Operational Amplifiers

DIP-8 Mechanical Drawing



DIP-8 DIMENSION					
DIM	MILLIMETERS		INCHES		
	MIN	MAX	MIN	MAX	
Α	9.07	9.32	0.357	0.367	
В	6.22	6.48	0.245	0.255	
С	3.18	4.45	0.125	0.135	
D	0.35	0.55	0.019	0.020	
G	2.54 (typ)		0.10 (typ)		
J	0.29	0.31	0.011	0.012	
К	3.25	3.35	0.128	0.132	
Ĺ	7.75	8.00	0.305	0.315	
М	-	10°	-	10°	

Marking Diagram



Y = Year Code

M = Month Code

(A=Jan, B=Feb, C=Mar, D=Apl, E=May, F=Jun, G=Jul, H=Aug, I=Sep,

J=Oct, **K**=Nov, **L**=Dec)

L = Lot Code



Single Supply Dual Operational Amplifiers

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.