

MOCD207

DESCRIPTION

The MOCD207 is a dual channel optically coupled isolator each channel consists of an infrared light emitting diode and a NPN silicon photo transistor in a space efficient dual in line plastic package.

It belongs to Isocom Compact Range of optocouplers

FEATURES


- Half Pitch 1.27mm
- High AC Isolation Voltage 3750V_{RMS}
- Wide Operating Temperature Range -55°C to +110°C
- Lead Free and RoHS Compliant
- UL Approval File E91231

APPLICATIONS

- Feedback Control Circuits
- Interfacing and Coupling Systems of Different Potentials and Impedances
- General Purpose Switching Circuits
- Monitor and Detection Circuits

ORDER INFORMATION

- Available in Tape and Reel with 2000pcs per reel



1, 3	Anode	5, 7	Emitter
2, 4	Cathode	6, 8	Collector

ABSOLUTE MAXIMUM RATINGS (T_A = 25°C)

Stresses exceeding the absolute maximum ratings can cause permanent damage to the device. Exposure to absolute maximum ratings for long periods of time can adversely affect reliability.

Input

Forward Current	60mA
Pulse Forward Current (t = 10μs)	1A
Reverse Voltage	6V
Power dissipation	90mW

Output

Output Current	50mA
Collector to Emitter Voltage BV _{CEO}	80V
Emitter to Collector Voltage BV _{CBO}	80V
Emitter to Collector Voltage BV _{ECO}	7V
Power Dissipation	150mW

Total Package

Isolation Voltage	3750V _{RMS}
Total Power Dissipation	250mW
Operating Temperature	-55 to 110°C
Storage Temperature	-55 to 125°C
Lead Soldering Temperature (10s)	260°C

ISOCOM COMPONENTS 2004 LTD

Unit 25B, Park View Road West, Park View Industrial Estate
Hartlepool, Cleveland, TS25 1UD, United Kingdom
Tel: +44 (0)1429 863 609 Fax: +44 (0)1429 863 581
e-mail: sales@isocom.co.uk
<http://www.isocom.com>

ISOCOM COMPONENTS ASIA LTD

Hong Kong Office
Block A, 8/F, Wah Hing Industrial Mansions
36 Tai Yau Street, San Po Kong, Kowloon, Hong Kong
Tel: +852 2995 9217 Fax: +852 8161 6292
e-mail sales@isocom.com.hk

MOCD207

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise specified)

INPUT

Parameter	Symbol	Test Condition	Min	*Typ.	Max	Unit
Forward Voltage	V_F	$I_F = 10\text{mA}$		1.2	1.5	V
Reverse Current	I_R	$V_R = 6\text{V}$		0.1	100	μA
Input Capacitance	C_{IN}	$V_F = 0\text{V}$, $f = 1\text{MHz}$		25		pF

OUTPUT

Parameter	Symbol	Test Condition	Min	*Typ.	Max	Unit
Collector-Emitter Breakdown Voltage	BV_{CEO}	$I_F = 0\text{mA}$, $I_C = 0.1\text{mA}$	80			V
Emitter-Collector Breakdown Voltage	BV_{ECO}	$I_F = 0\text{mA}$, $I_E = 0.1\text{mA}$	7			V
Collector-Emitter Dark Current	I_{CEO}	$I_F = 0\text{mA}$, $V_{CE} = 10\text{V}$		5.0	50	nA
Collector-Emitter Capacitance	C_{CE}	$V_{CE} = 0\text{V}$, $f = 1\text{MHz}$		10		pF

COUPLED

Parameter	Symbol	Test Condition	Min	*Typ.	Max	Unit
Current Transfer Ratio	CTR	$I_F = 10\text{mA}$, $V_{CE} = 5\text{V}$	100		200	%
		$I_F = 1\text{mA}$, $V_{CE} = 5\text{V}$	34	70		
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_F = 10\text{mA}$, $I_C = 2.5\text{mA}$			0.4	V
Input-Output Capacitance	C_{IO}	$V_{IO} = 0\text{V}$, $f = 1\text{MHz}$		0.5		pF
Turn-On Time	t_{ON}	$V_{CC} = 10\text{V}$ $I_C = 2\text{mA}$ $R_L = 100\Omega$		5		μs
Turn-Off Time	t_{OFF}			4		
Output Rise Time	t_r			1.6		
Output Fall Time	t_f			2.2		

ISOLATION

Parameter	Symbol	Test Condition	Min	*Typ.	Max	Unit
Input to Output Isolation Voltage	V_{ISO}	RH = 40% - 60%, $t = 1\text{ min}$ Note 1	3750			V_{RMS}
Input to Output Isolation Resistance	R_{ISO}	$V_{IO} = 500\text{V}$ Note 1		10^{11}		Ω

Note 1 : Measured with input leads 1, 2, 3, 4 shorted together and output leads 5, 6, 7, 8 shorted together.

* Typical values at $T_A = 25^\circ\text{C}$




Fig 1 Collector Current vs Collector-emitter Voltage (1)




Fig 2 Collector Current vs Collector-emitter Voltage (2)




Fig 3 Normalized Collector Current vs Forward Current




Fig 4 Normalized Collector Current vs T_A




Fig 5 Forward Current vs Forward Voltage




Fig 6 Collector Dark Current vs T_A






Fig 7 Turn-On and Turn-Off Times vs Load Resistance




Switching Time Test Circuit and Waveforms

MOCD207

ORDER INFORMATION

MOCD207			
After PN	PN	Description	Packing quantity
None	MOCD207	Surface Mount Tape & Reel	2000 pcs per reel


DEVICE MARKING




D207 denotes Device Part Number
/ denotes Isocom
Y denotes 1 digit Year code
WW denotes 2 digit Week code

MOCD207

PACKAGE DIMENSIONS (mm)





RECOMMENDED PAD LAYOUT (mm)




MOCD207

TAPE AND REEL PACKAGING




Direction of feed from reel



Dimension No.	A0	A1	B0	D0	D1	E	F
Dimension (mm)	6.2±0.1	4.1±0.1	5.28±0.1	1.5±0.1	1.5±0.3	1.75±0.1	5.5±0.1
Dimension No.	Po	P1	P2	t	W	K0	K1
Dimension (mm)	4.0±0.1	8.0±0.1	2.0±0.1	0.4±0.1	12.0 +0.3/-0.1	3.7±0.1	0.3±0.1



IR REFLOW SOLDERING TEMPERATURE PROFILE FOR SMD
(One Time Reflow Soldering is Recommended)



Profile Details	Conditions
Preheat - Min Temperature (T_{SMIN}) - Max Temperature (T_{SMAX}) - Time T_{SMIN} to T_{SMAX} (t_s)	150°C 200°C 60s - 120s
Soldering Zone - Peak Temperature (T_P) - Liquidous Temperature (T_L) - Time within 5°C of Actual Peak Temperature (T_P - 5°C) - Time maintained above T_L (t_L) - Ramp Up Rate (T_L to T_P) - Ramp Down Rate (T_P to T_L)	260°C 217°C 30s 60s - 100s 3°C/s max 6°C/s max
Average Ramp Up Rate (T _{smax} to T _P)	3°C/s max
Time 25°C to Peak Temperature	8 minutes max

DISCLAIMER

Isocom Components is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing Isocom Components products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such Isocom Components products could cause loss of human life, bodily injury or damage to property.

In developing your designs, please ensure that Isocom Components products are used within specified operating ranges as set forth in the most recent Isocom Components products specifications.

The Isocom Components products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These Isocom Components products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation Instruments, traffic signal instruments, combustion control instruments, medical Instruments, all types of safety devices, etc... Unintended Usage of Isocom Components products listed in this document shall be made at the customer's own risk.

Gallium arsenide (GaAs) is a substance used in the products described in this document. GaAs dust and fumes are toxic. Do not break, cut or pulverize the product, or use chemicals to dissolve them. When disposing of the products, follow the appropriate regulations. Do not dispose of the products with other industrial waste or with domestic garbage.

The products described in this document are subject to the foreign exchange and foreign trade laws.

The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by Isocom Components for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of Isocom Components or others.

The information contained herein is subject to change without notice.