
# 55/2124-28-6/9-9 Product Details





Active

## Spec 44, Spec 55 and Spec RCW Wire and Cable

55/2124-28-6/9-9

**55/2124-28-6/9-9**

*TE Internal Number: 381687-000*

**Product Highlights** View All

- Cable Type = Spec 55
- Wire Source = United States
- Cable Style = Flat Braid Shielded and Jacketed
- Wire Size (AWG/CM) = 28 AWG
- Voltage Rating = 600 VAC

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

[+] Feedback

Documents | Features | Compliance

**Please Note:**
*Use the Product Drawing for all design activity*

### Product Type Features

| | |
|---|---|
| **Cable Type** | Spec 55 |
| **Cable Style** | Flat Braid Shielded and Jacketed |

### Electrical Characteristics

| | |
|---|---|
| **Voltage Rating (VAC)** | 600 |

### Body Features

| | |
|---|---|
| **Wire Size (AWG/CM)** | 28 AWG |
| **Cable Jacket Color** | White |
| **Conductor Type** | Silver-Coated High Strength Copper Alloy |
| **Wire Color** | Blue, White |
| **Nominal Outside Diameter (mm [in])** | 1.96 [0.077] |
| **Wire Diameter (mm [in])** | 0.69 [0.027] |
| **Shield Size** | 34 AWG |
| **Shield Material** | Tin Plated Copper |

### Configuration Features

| | |
|---|---|
| **Number of Conductors** | 2 |

### Industry Standards

| | |
|---|---|
| **Government/Industry Qualification** | No |
| **RoHS/ELV Compliance** | Not reviewed for ELV/RoHS compliance |
| **Lead Free Solder Processes** | Not relevant for lead free process |

### Conditions for Usage

| | |
|---|---|
| **Temperature Range (°C)** | -65 – +200 |

### Operation/Application

| | |
|---|---|
| **Application** | Space Applications |

### Packaging Features

| | |
|---|---|
| **Wire Source** | United States |

### Other

| | |
|---|---|
| **Brand** | Raychem |

**Related Products**

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling





© 2014 TE Connectivity Ltd. family of companies. All Rights Reserved

[+] Provide Website Feedback

Downloaded from Arrow.com.