





PRODUCT NUMBER	PITCH
YK421xx0x0J0G	8.25 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

MATERIALS & ELECTRICAL
 RATED VOLTAGE & CURRENT: 300 V, 20 A
 WITHSTAND VOLTAGE: AC 2000 V/Min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 8.8 Lb-In.
 WIRE RANGE: 22 - 12 AWG
 1) HOUSING: THERMOPLASTIC, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M3
 APPROVAL: US

DIMENSION

Dim A	N×8.25±1.72
Dim B	(N-1)×8.25

N=Number of poles

Poles	Tolerance
2p-8p	±0.30
9p-16p	±0.40
17p-24p	±0.50
25p-32p	±0.60

PART NO.: YK 421xx 0 x 0 J0G

No. of poles
 02 2 poles
 03 3 poles
 ...
 32 32 poles

Plated

Code	Terminal	Screw
0	G/F	G/F
1	G/F	Zinc
2	Tin	G/F
3	Tin	Zinc

RoHS compliant
 (lead<4%)
 In copper Alloy

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK																											
ltr		ecn no		dr		date		tolerances unless otherwise specified								title TERMINAL BLOCK																					
								angles		lineal		X.±0.5																									
								X.X±0.3																													
								X*±1°				X.XX±0.1																									
								dr		EVAN LU		061314				dwg no										sheet 1 of 1		size									
								engr		EVAN LU		061314				YK421xx0x0J0G										A											
								chr		HANKE FENG		061314																									
								appd		SHI JUN		061314																									
sheet index		revision sheet		A 1														type										CUSTOMER Drawing									