

FW1220G06 Product Details



FW1220G06
(2-1617020-8)
TE Internal Number: 2-1617020-8
Active

Military/Aerospace High Performance Relays

Not EU RoHS or ELV Compliant

Product Highlights:

- FW Full Size Relay Series
- Input Voltage = 26.5 VDC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Current Rating = 2 A
- Non Polarized, Monostable Coil Magnetic System

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information

- Product Drawings:
- None Available

- Catalog Pages/Data Sheets:
- RELAY (PDF, English)

- Product Specifications:
- None Available

- Application Specifications:
- None Available

- Instruction Sheets:
- None Available

- CAD Files:
- None Available

- Additional Information:
- Product Line Information

- Related Products:
- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

- Product Type Features:
- Termination Type = PC Pins
- Electrical Characteristics:
- Input Voltage (VDC) = 26.5
 - Contact Current Rating (A) = 2
 - Coil Polarity Protection Diode = Without
 - Transistor Driver = Without
 - Coil Resistance (Ω) = 675
 - MOSFET Driver = Without
 - Coil Power Measurement = Milliwatts
 - Coil Power, Nominal (mW) = 1040
 - Actuating System = DC
 - Shock = 100G's, 6ms
 - Vibration = 20G's, 10 to 2000Hz
- Body Related Features:
- Series = FW Full Size Relay
- Contact Related Features:
- Mounting Options = Chassis Mount
 - Enclosure Type = Hermetically Sealed
 - Approved Standards = M5757 Qualified

- Configuration Related Features:
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
 - Coil Magnetic System = Non Polarized, Monostable
 - Coil Suppression Diode = Without
- Industry Standards:
- Government/Industry Qualification = Yes
 - Government/Industry Part Number = M5757/10-040
 - RoHS/ELV Compliance = Not ELV/RoHS compliant
 - Lead Free Solder Processes = Not suitable for lead free processing
- Conditions for Usage:
- Temperature Range (°C) = -65 - +125
- Other:
- Brand = CII

BOOKMARK

Corporate Information

- Who We Are
- Investors
- News Room
- Supplier Portal
- Careers

Quick Links

- Check Distributor Inventory
- Cross Reference
- Find Documents & Drawings
- Product Compliance Support Center
- Site Map

Customer Support

- Email or Chat with Us
- Find a Phone Number
- Search Knowledge Base
- Manage Your Account

Sign up for our eNewsletter

Enter your email address

Follow us on:

