

Part Number : 192030011
Product Description : Krimptite Temp-Term Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : A-S-132-06T

Documents and Resources

Drawings

192030011_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-011-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Temp-Term Ring Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring, High Temperature
Type	High Temperature Terminal
UPC	800753049406

Agency

UL	E32244

Electrical

Voltage - Maximum	up to 35kV

Physical

Barrel Type	Closed
Insulation	None
Material - Metal	Steel
Material - Plating Mating	Nickel

Downloaded from Arrow.com.

Net Weight	0.508/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	6 (M3.5)
Temperature Range - Operating	-50° to +483°C
Termination Interface Style	Crimp or Compression
Wire Size (AWG)	18, 20, 22
Wire Size mm^2	0.25-1.50

Solder Process Data

Lead-Free Process Capability	N/A

Application Tooling

Global

Description	Part Number
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	190270026
Mini-Mac Applicator	638854500

Downloaded from Arrow.com.