

# FSRH030060RNB00#

“#” indicates a package specification code.

Discontinued

RoHS

REACH


## < List of part numbers with package codes >

FSRH030060RNB00B

## Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	Consumer equipment, Medical [Ask Murata] Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

## Appearance & Shape



## Packaging Information

Packaging	Specifications	Standard Packing Quantity
B	Bulk(Bag)	10000

## Features

### Features

1. Ease of use and excellent noise suppression-data lines can be passed through the core or wound around several times.
2. Effective for suppressing noise at high frequencies.

### Applications

1. For Data-processing equipment (PC, PDA, Game machine, etc.), and peripheral equipments (Printer, HDD, Display, etc.)
2. For digital equipments (DSC, DVC, DVD recorder, Mobile phone, Digital audio, Optical drive, PDP/LCD/FED, facsimile, etc.)

### Attention


1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# FSRH030060RNB00#

“#” indicates a package specification code.



## Specifications

Material	RN
Mass	0.24g
Impedance at 10MHz(typ.)	41Ω (1Turn)
Impedance at 100MHz(typ.)	74Ω (1Turn)
Core Type	Beads core
A : Outer Dimension	3.36mm
A : Outer Dimension Tolerance	±0.15mm
B : Inner Dimension	1.1mm
B : Inner Dimension Tolerance	±0.15mm
H : Length Dimension	6.0mm
H Length Dimension Tolerance	±0.2mm
USB/IEEE1394	No

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.



Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# FSRH030060RNB00#

“#” indicates a package specification code.



## Product Data



### Impedance-Frequency Characteristics

### Cases to use

#### Attention

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.