



E32-A01 5M

Fiber optic sensor head, liquid level detection, tube mounting 3.2; 6.4 and 9.5mm diameter, R4 bend resistant fiber, 5 m cable

Specifications

Sensing method	Through-beam
Shape	Square
Application	Liquid level detection
Features	Bend resistant
Temperature range	-40-70 °C
Cable length	5 m
Bending radius	4 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP50
Material sheath	Fluororesin

Related products



E3X-ZV and E3X-MZV

Smart Fiber Amplifier



E3NX-CA

High-performance color
mark sensor



E3NX-CA

High-performance color
mark sensor



E3NX-MA

Smart Fiber Amplifier Units



E3NX-FA

High-performance digital
fiber amplifier



E3X-NA

Digital fiber amplifier with
potentiometer adjustment

Downloads

CAD Library



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Fiber Sensor Selection Selection Guide

EN PDF 16.2 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 20 June, 2025. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | [INDUSTRIAL.OMRON.EU](https://industrial.omron.eu)