SIEMENS

Data sheet 3SU1400-1AA10-1DA0

Siemens EcoTech



Contact module with 2 contact elements, 2 NO, screw terminal, for front plate mounting

product brand name	SIRIUS ACT
product designation	Contact module
product type designation	3SU1
Contact block/ lampholder	
socket design	other
General technical data	
product function positive opening	No
insulation voltage rated value	500 V
degree of pollution	3
type of voltage	
● of the operating voltage	AC/DC
● of the input voltage	AC/DC
surge voltage resistance rated value	6 kV
protection class IP	
● of the enclosure	IP40
● of the terminal	IP20, clamping screw tightened
shock resistance	
● **according to IEC 60068-2-27**	sinusoidal half-wave 15 g / 11 ms
● for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
● **according to IEC 60068-2-6**	10 ... 500 Hz: 5 g
● for railway applications according to EN 61373	Category 1, Class B
operating frequency maximum	3 600 1/h
mechanical service life (operating cycles) typical	10 000 000
electrical endurance (operating cycles) typical	10 000 000
thermal current	10 A
reference code according to IEC 81346-2	S
continuous current of the C characteristic MCB	10 A
Substance Prohibitance (Date)	10/01/2014
Net Weight	17 g
operating voltage	
● at AC	
— at 50 Hz rated value	5 ... 500 V
— at 60 Hz rated value	5 ... 500 V
● **at DC rated value**	5 ... 500 V
Power Electronics	

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

contact reliability	One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)
Auxiliary circuit	
design of the contact of auxiliary contacts	Silver alloy
number of NC contacts for auxiliary contacts	0
● lagging switching	0
number of NO contacts for auxiliary contacts	2
● leading contact	0
operational current at AC-12	
● at 24 V rated value	10 A
● at 48 V rated value	10 A
● at 110 V rated value	10 A
● at 230 V rated value	8 A
● at 400 V rated value	8 A
operational current at AC-15	
● at 24 V rated value	6 A
● at 48 V rated value	6 A
● at 110 V rated value	6 A
● at 230 V rated value	6 A
● at 400 V rated value	3 A
● at 500 V rated value	1.4 A
operational current at DC-12	
● at 24 V rated value	10 A
● at 48 V rated value	5 A
● at 110 V rated value	2.5 A
● at 230 V rated value	1 A
● at 400 V rated value	0.3 A
● at 500 V rated value	0.3 A
operational current at DC-13	
● at 24 V rated value	3 A
● at 48 V rated value	1.5 A
● at 110 V rated value	0.7 A
● at 230 V rated value	0.3 A
● at 400 V rated value	0.1 A
● at 500 V rated value	0.1 A
Connections/ Terminals	
type of electrical connection	screw terminal
type of connectable conductor cross-sections	
● solid with core end processing	2x (0.5 ... 0.75 mm²)
● solid without core end processing	2x (1.0 ... 1.5 mm²)
● finely stranded with core end processing	2x (0.5 ... 1.5 mm²)
● finely stranded without core end processing	2x (1,0 ... 1,5 mm²)
● for AWG cables	2x (18 ... 14)
tightening torque with screw-type terminals	0.8 ... 0.9 N·m
Ambient conditions	
ambient temperature	
● during operation	-25 ... +70 °C
● during storage	-40 ... +80 °C
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3 (without salt spray), 3K6 (with relative humidity of 10 ... 95%, no condensation in operation permitted)
Installation/ mounting/ dimensions	
fastening method	front plate mounting
● of modules and accessories	Front plate mounting
height	34 mm
width	9.8 mm
depth	49.7 mm
suitability for integration	
● plastic enclosure	No
● metal enclosure	No

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

Approvals Certificates

Environmental Product Declaration

• global warming potential [CO2 eq] / during manufacturing	0.566 kg
• global warming potential [CO2 eq] / during operation	0.235 kg
• global warming potential [CO2 eq] / after end of life	-0.0145 kg
• global warming potential [CO2 eq] / total	0.787 kg

Environment

Environmental Confirmations

General Product Approval

General Product Approval

Test Certificates

Type Test Certificates/Test Report

Special Test Certificate

Maritime application

other


Confirmation


Confirmation

Further information

Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1400-1AA10-1DA0
Cax online generator
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1400-1AA10-1DA0
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3SU1400-1AA10-1DA0
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1400-1AA10-1DA0&lang=en

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.





last modified: 4/4/2026

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.