





RoHS Compliant

N=NUMBER OF CONTACTS

DIM		TOL		
		2P	3P-4P	5P-8P
Dim L	N×15.0-5.0	±0.50	±0.50	±0.60
Dim P	(N-1)×15.0	±0.25	±0.50	±0.60



RECOMMENDED PCB LAYOUT

REV	SIGN	DATE	DESCRIPTION	APPROVER
D	△	2019.09.27	Modify the Struction	LENA
E	△	2021.11.01	Add TUV certification	Rhine
THIS IS CAD DRAWING, DO NOT REVISE MANUALL Y!!!				

Material:

- Item a Lever: Thermoplastic (UL 94V-0),
 - Item b Cam: Thermoplastic (UL 94V-0),
 - Item c Middle Body: Thermoplastic (UL 94V-0),
 - Item d Left side body: Thermoplastic (UL 94V-0),
 - Item e Right side body: Thermoplastic (UL94V-0),
 - Item f Base board: Thermoplastic (UL 94V-0)
 - Item g Contact: Copper,Matte Tin plated over Nickel plated,
 - Item h Spring clamp: Stainless steel
- △ Electrical: cULus TUV(EN/IEC 60947-7-4)
- Voltage rating: 600 V 800V (III/3) 1000V(III/2) 1000V(II/2)
 - Current rating: 65A 76A
 - Wire range(AWG): 16-6 (Solid & Stranded)
 - Wire range: 0.75mm²-10mm²(Flexible) 0.75mm²-16mm²(Solid & Rigid stranded)
 - Wire strip length: 12-13 mm
 - Withstanding Voltage: 2.2KV 4.2KV
 - Rated impulse Withstanding Voltage: 8KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 260°C±5°C/5 Sec
 - Safety Approval: △
 - Critical dimension: △
 - Part No.:

NZ XX 1 0 X B XXXX G

No. OF POLES	Body	Color	RoHS compliant
01 1 Poles	0 Black (RAL9005)	2 Red (RAL3001/D)	(lead<4%)
08 8 Poles	3 Orange(RAL2011/P)	4 Yellow(RAL1018/A)	In copper Alloy
	5 Green(RAL6018/T)	6 Blue (RAL5015/A)	0000: "@" Logo (Standard)
	8 Grey(RAL7004/P)	9 White(RAL1102)	000A: "ANYTEK" Mark
	C Multiple colors		

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	NZ 15.0 Series without jumper slot (1P-8P)						
PART NO.	NZ XX10XBXXXXG			DWG NO.	8NZ0004		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Rhine 2021.11.01	Rhine 2021.11.01		UNIT: mm	X. ±0.50	
				SCALE: 1:1		X.X ±0.30	
				SHEET: 01/01	REV.: E	X.XX ±0.10	
						X* ±1°	