Part Number : 1054550101
Product Description : Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Mid-Mount, Surface Mount, Gold (Au) Flash over 0.75µm Palladium Nickel Plating, 0.70mm Solder Tab, Paper Reel
Series Number : 105455
Status : Active
Product Category : I/O Connectors



Documents and Resources

Drawings

1054550101_sd.pdf

PK-105455-001-000.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PS-105448-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

Downloaded from Arrow.com.

- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	I/O Connectors
Series	105455
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right-Angle, Mid-Mount, Surface Mount, Gold (Au) Flash over 0.75µm Palladium Nickel Plating, 0.70mm Solder Tab, Paper Reel
Application	Wire-to-Board
Component Type	Receptacle
Product Name	USB
Standard	USB 3.2 Gen 2
Type	C
UPC	889056733250

Electrical

Current - Maximum per Contact	0.25A, 1.25A, 5.0A
Grounding to Panel	No
Shielded	Yes
Shield Type	Full Shield
Voltage - Maximum	30V AC/DC

Downloaded from Arrow.com.

Physical

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Palladium Nickel
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Mounting Style	Mid-Mount
Net Weight	0.530/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	0.60mm, 0.70mm, 0.80mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.051µm (Au), 0.750µm (PdNi)
Plating min - Termination	0.051µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-30° to +85°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No

Mates With / Use With

Mates with Part(s)

Downloaded from Arrow.com.

Description	Part Number
Universal Serial Bus (USB) Shielded I/O Plug, Type C, Right-Angle, Surface Mount, 0.76µm Gold (Au) Plating, Tray	1054440001
Universal Serial Bus (USB) Shielded I/O Plug, Type C, Right-Angle, Surface Mount, 0.76µm Gold (Au) Plating, Tape and Reel	1054440011

Downloaded from Arrow.com.