

Access Point - RAD-80211-XDB



2990011

<https://www.phoenixcontact.com/us/products/2990011>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



WLAN access point, 24 V DC; IEEE 802.11 a/b/g; 2.4 GHz; 5 GHz, client adapter, bridge; antenna diversity; Wi-Fi compliant; web-based management; 802.11i, DIN rail mounting, without antenna

Your advantages

- Protected against manipulation and tapping
- High performance and reliability
- Long range
- Excellent integration in automation systems

Access Point - RAD-80211-XDB



2990011

<https://www.phoenixcontact.com/us/products/2990011>

Commercial Data

Item number	2990011
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	C23
Product Key	DNN2W2
Catalog Page	Page 125 (AX-2011)
GTIN	4046356323178
Weight per Piece (including packing)	327.8 g
Weight per Piece (excluding packing)	327.8 g
Customs tariff number	85176200
Country of origin	CA

Access Point - RAD-80211-XDB

2990011

<https://www.phoenixcontact.com/us/products/2990011>



Technical Data

Product properties

Product type	Wireless module
--------------	-----------------

Electrical properties

Supply: Module electronics

Connection method	Via COMBICON
Supply voltage	24 V DC
Supply voltage range	9 V DC ... 30 V DC
Supply current	215 mA (24 V DC) 468 mA (9 V DC)

Interfaces

Ethernet

Number	1
Connection method	RJ45 jack

Antenna

Number	1
--------	---

Functions

Operating modes	Access point, client, bridge
Configuration	Web-based management
Automatic channel selection	Yes
Security	WEP 64 bit/128 bit WPA TKIP 802.11i WPA2 (AES) WPA PSK (preshared key)
Wireless licenses	Americas, more countries in E-shop
Country support	USA Canada
Connection method	D-SUB 9, COMBICON
Protocols supported	RS-232, RS-485, RS-422

Wireless

Antenna connection method	2x MCX (female)
Wireless standard	IEEE 802.11 a b g h
Transmission power	20 dBm (EIRP)
Number of wireless interfaces	1 IEEE 802.11 a/b/g

Access Point - RAD-80211-XDB



2990011

<https://www.phoenixcontact.com/us/products/2990011>

Dimensions

Width	45 mm
Height	99 mm
Depth	113 mm

Material specifications

Color	green
-------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 65 °C
Air pressure (operation)	795 hPa ... 1080 hPa (up to 2000 m above sea level)
Permissible humidity (operation)	5 % ... 90 % (non-condensing)

Approval data

Conformity/Approvals

UL, USA / Canada	Class I, Div. 2, Groups A, B, C, D T5
FCC	Part 15

Mounting

Mounting type	DIN rail mounting
Assembly instructions	Antenna not included

Phoenix Contact 2022 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com