



**Part Number :** [1202530200](#)  
**Product Description :** Contrinex Inductive Sensor,  
M8 Housing, 1.5mm Operating Distance, Embeddable,  
PNP, NO, 2m 3-wire PVC Cable, 35mm Housing Length  
**Series Number :** 120253  
**Status :** Not Recommended For New Design  
**Product Category :** Inductive and Photoelectric  
Sensors  
**Engineering Number :** DW-AD-603-M8

## Documents & Resources

### Specifications

[1202530198-000.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                              |
|--------------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                                 |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                                 |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21                                                                              |
| REACH SVHC         | Not Reviewed per D(2025)4165-DC<br>(25 June 2025)                                                            |
| EU RoHS            | Compliant per EU 2015/863                                                                                    |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

## UKCA - Declaration of Conformity

## CE - Declaration of Conformity

---

## Part Details

### General

|              |                                                                                                                                 |
|--------------|---------------------------------------------------------------------------------------------------------------------------------|
| Status       | Not Recommended For New Design                                                                                                  |
| Category     | Inductive Sensors                                                                                                               |
| Series       | 120253                                                                                                                          |
| Description  | Contrinex Inductive Sensor, M8 Housing, 1.5mm Operating Distance, Embeddable, PNP, NO, 2m 3-wire PVC Cable, 35mm Housing Length |
| IP Rating    | IP67                                                                                                                            |
| Product Name | Contrinex                                                                                                                       |
| Type         | Inductive                                                                                                                       |
| UPC          | 191130063703                                                                                                                    |

### Electrical

|                     |           |
|---------------------|-----------|
| Output              | NO        |
| Polarity            | PNP       |
| Switching Frequency | ≤ 5000 Hz |

### Physical

|                         |                        |
|-------------------------|------------------------|
| Connection              | Cable (PVC 2m, 3-wire) |
| Length                  | 35mm                   |
| Material - Housing      | Stainless Steel        |
| Material - Sensing Face | PA66                   |
| Mounting Style          | Embeddable             |
| Net Weight              | 41.500/g               |
| Operating Distance      | 1.5mm                  |
| Output                  | NO                     |

|                               |               |
|-------------------------------|---------------|
| Sensor Housing Size           | M8            |
| Temperature Range - Operating | -25° to +70°C |

---

This document was generated on Sep 22, 2025