

# Si/SiC Hybrid Modules – EliteSiC, 3 Channel Flying Capacitor Boost 1000 V, 100 A IGBT, 1200 V, 30 A SiC Diode, Q2 Package NXH300B100H4Q2F2, NXH300B100H4Q2F2SG-R


This high-density, integrated power module combines high-performance IGBTs with 1200 V SiC diode.

## Features


- Extremely Efficient Trench with Field Stop Technology
- Low Switching Loss Reduces System Power Dissipation
- Module Design Offers High Power Density
- Low Inductive Layout
- 3-channel in Q2BOOST Package
- These are Pb-Free Devices

## Typical Applications

- Solar Inverter
- Uninterruptible Power Supplies




PIM53, 93x47 (PRESSFIT)  
CASE 180CB



PIM53, 93x47 (SOLDER PIN)  
CASE 180CC


## MARKING DIAGRAM



NXH300B100H4Q2F2x = Specific Device Code  
(x = P, S)

AT = Assembly & Test Site Code  
YYWW = Year and Work Week Code

## PIN CONNECTION



## ORDERING INFORMATION

See detailed ordering and shipping information on page 11 of this data sheet.




Figure 1. NXH300B100H4Q2F2PG/SG/SG-R Schematic Diagram

# NXH300B100H4Q2F2, NXH300B100H4Q2F2SG-R

## ABSOLUTE MAXIMUM RATINGS (Note 1) ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Symbol                                     | Parameter                                                                                                           | Value          | Unit             |
|--------------------------------------------|---------------------------------------------------------------------------------------------------------------------|----------------|------------------|
| <b>IGBT (T11, T21, T12, T22, T13, T23)</b> |                                                                                                                     |                |                  |
| $V_{CES}$                                  | Collector-Emitter voltage                                                                                           | 1000           | V                |
| $V_{GE}$                                   | Gate-Emitter Voltage<br>Positive transient gate-emitter voltage ( $T_{\text{pulse}} = 5 \mu\text{s}$ , $D < 0.10$ ) | $\pm 20$<br>30 | V                |
| $I_C$                                      | Continuous Collector Current (@ $V_{GE} = 20 \text{ V}$ , $T_C = 80^\circ\text{C}$ )                                | 73             | A                |
| $I_{C(\text{Pulse})}$                      | Pulsed Peak Collector Current @ $T_C = 80^\circ\text{C}$ ( $T_J = 150^\circ\text{C}$ )                              | 219            | A                |
| $P_{\text{tot}}$                           | Power Dissipation ( $T_J = 150^\circ\text{C}$ , $T_C = 80^\circ\text{C}$ )                                          | 194            | W                |
| $T_{J\text{MIN}}$                          | Minimum Operating Junction Temperature                                                                              | -40            | $^\circ\text{C}$ |
| $T_{J\text{MAX}}$                          | Maximum Operating Junction Temperature                                                                              | 175            | $^\circ\text{C}$ |

## IGBT INVERSE DIODE (D11, D21, D12, D22, D13, D23) AND BYPASS DIODE (D51, D61, D52, D62, D53, D63)

|                   |                                                                                                    |      |                  |
|-------------------|----------------------------------------------------------------------------------------------------|------|------------------|
| $V_{RRM}$         | Peak Repetitive Reverse Voltage                                                                    | 1600 | V                |
| $I_F$             | Continuous Forward Current @ $T_C = 80^\circ\text{C}$                                              | 36   | A                |
| $I_{FRM}$         | Repetitive Peak Forward Current ( $T_J = 150^\circ\text{C}$ , $T_J$ limited by $T_{J\text{max}}$ ) | 108  | A                |
| $P_{\text{tot}}$  | Maximum Power Dissipation @ $T_C = 80^\circ\text{C}$ ( $T_J = 150^\circ\text{C}$ )                 | 79   | W                |
| $T_{J\text{MIN}}$ | Minimum Operating Junction Temperature                                                             | -40  | $^\circ\text{C}$ |
| $T_{J\text{MAX}}$ | Maximum Operating Junction Temperature                                                             | 150  | $^\circ\text{C}$ |

## BOOST SILICON CARBIDE SCHOTTKY DIODE (D31, D41, D32, D42, D33, D43)

|                   |                                                                                                    |      |                  |
|-------------------|----------------------------------------------------------------------------------------------------|------|------------------|
| $V_{RRM}$         | Peak Repetitive Reverse Voltage                                                                    | 1200 | V                |
| $I_F$             | Continuous Forward Current @ $T_C = 80^\circ\text{C}$                                              | 36   | A                |
| $I_{FRM}$         | Repetitive Peak Forward Current ( $T_J = 150^\circ\text{C}$ , $T_J$ limited by $T_{J\text{max}}$ ) | 108  | A                |
| $P_{\text{tot}}$  | Maximum Power Dissipation @ $T_C = 80^\circ\text{C}$ ( $T_J = 150^\circ\text{C}$ )                 | 104  | W                |
| $T_{J\text{MIN}}$ | Minimum Operating Junction Temperature                                                             | -40  | $^\circ\text{C}$ |
| $T_{J\text{MAX}}$ | Maximum Operating Junction Temperature                                                             | 175  | $^\circ\text{C}$ |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe Operating parameters.

## THERMAL AND INSULATION PROPERTIES (Note 1) ( $T_J = 25^\circ\text{C}$ unless otherwise noted)

| Symbol                    | Rating                                          | Value      | Unit             |
|---------------------------|-------------------------------------------------|------------|------------------|
| <b>THERMAL PROPERTIES</b> |                                                 |            |                  |
| $T_{VJOP}$                | Operating Temperature under Switching Condition | -40 to 150 | $^\circ\text{C}$ |
| $T_{\text{stg}}$          | Storage Temperature Range                       | -40 to 125 | $^\circ\text{C}$ |

## INSULATION PROPERTIES

|                 |                                                              |      |                  |
|-----------------|--------------------------------------------------------------|------|------------------|
| $V_{\text{is}}$ | Isolation Test Voltage, $t = 2 \text{ sec}$ , 50 Hz (Note 3) | 4000 | $V_{\text{RMS}}$ |
|                 | Creepage Distance                                            | 12.7 | mm               |
| CTI             | Comparative Tracking Index                                   | >600 |                  |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

2. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe Operating parameters.
3. 4000  $V_{\text{ACRMS}}$  for 1 second duration is equivalent to 3333  $V_{\text{ACRMS}}$  for 1 minute duration.

# NXH300B100H4Q2F2, NXH300B100H4Q2F2SG-R

## ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25°C unless otherwise noted)

| Symbol                                                                                            | Parameter                             | Test Condition                                                                                                                  | Min  | Typ   | Max  | Unit |
|---------------------------------------------------------------------------------------------------|---------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|------|-------|------|------|
| IGBT (T11, T21, T12, T22, T13, T23)                                                               |                                       |                                                                                                                                 |      |       |      |      |
| V <sub>(BR)CES</sub>                                                                              | Collector–Emitter Breakdown Voltage   | V <sub>GE</sub> = 0 V, I <sub>C</sub> = 1 mA                                                                                    | 1000 | 1118  | –    | V    |
| V <sub>CE(SAT)</sub>                                                                              | Collector–Emitter Saturation Voltage  | V <sub>GE</sub> = 15 V, I <sub>C</sub> = 100 A, T <sub>C</sub> = 25°C                                                           | –    | 1.80  | 2.25 | V    |
|                                                                                                   |                                       | V <sub>GE</sub> = 15 V, I <sub>C</sub> = 100 A, T <sub>C</sub> = 150°C                                                          | –    | 2.03  | –    |      |
| V <sub>GE(TH)</sub>                                                                               | Gate–Emitter Threshold Voltage        | V <sub>GE</sub> = V <sub>CE</sub> , I <sub>C</sub> = 100 mA                                                                     | 4.1  | 5.08  | 5.9  | V    |
| I <sub>CES</sub>                                                                                  | Collector–Emitter Cutoff Current      | V <sub>GE</sub> = 0 V, V <sub>CE</sub> = 1000 V                                                                                 | –    | –     | 800  | μA   |
| I <sub>GES</sub>                                                                                  | Gate Leakage Current                  | V <sub>GE</sub> = ±20 V, V <sub>CE</sub> = 0 V                                                                                  | –    | –     | ±400 | nA   |
| r <sub>g</sub>                                                                                    | Internal Gate Resistor                |                                                                                                                                 | –    | 5     | –    | Ω    |
| t <sub>d(on)</sub>                                                                                | Turn–On Delay Time                    | T <sub>J</sub> = 25°C<br>V <sub>CE</sub> = 600 V, I <sub>C</sub> = 50 A<br>V <sub>GE</sub> = –9 V, +15 V, R <sub>G</sub> = 6 Ω  | –    | 95    | –    | ns   |
| t <sub>r</sub>                                                                                    | Rise Time                             |                                                                                                                                 | –    | 15.42 | –    |      |
| t <sub>d(off)</sub>                                                                               | Turn–Off Delay Time                   |                                                                                                                                 | –    | 267   | –    |      |
| t <sub>f</sub>                                                                                    | Fall time                             |                                                                                                                                 | –    | 59    | –    |      |
| E <sub>on</sub>                                                                                   | Turn on switching loss                |                                                                                                                                 | –    | 1030  | –    | μJ   |
| E <sub>off</sub>                                                                                  | Turn off switching loss               |                                                                                                                                 | –    | 1200  | –    |      |
| t <sub>d(on)</sub>                                                                                | Turn–On Delay Time                    | T <sub>J</sub> = 125°C<br>V <sub>CE</sub> = 600 V, I <sub>C</sub> = 50 A<br>V <sub>GE</sub> = –9 V, +15 V, R <sub>G</sub> = 6 Ω | –    | 97    | –    | ns   |
| t <sub>r</sub>                                                                                    | Rise Time                             |                                                                                                                                 | –    | 18    | –    |      |
| t <sub>d(off)</sub>                                                                               | Turn–Off Delay Time                   |                                                                                                                                 | –    | 314   | –    |      |
| t <sub>f</sub>                                                                                    | Fall time                             |                                                                                                                                 | –    | 93    | –    |      |
| E <sub>on</sub>                                                                                   | Turn on switching loss                |                                                                                                                                 | –    | 1260  | –    | μJ   |
| E <sub>off</sub>                                                                                  | Turn off switching loss               |                                                                                                                                 | –    | 2140  | –    |      |
| C <sub>ies</sub>                                                                                  | Input capacitance                     | V <sub>CE</sub> =20 V, V <sub>GE</sub> = 0 V, f = 1 MHz                                                                         | –    | 6323  | –    | pF   |
| C <sub>oes</sub>                                                                                  | Output capacitance                    |                                                                                                                                 | –    | 241   | –    |      |
| C <sub>res</sub>                                                                                  | Reverse transfer capacitance          |                                                                                                                                 | –    | 34    | –    |      |
| Q <sub>g</sub>                                                                                    | Gate Charge                           | V <sub>CE</sub> = 600 V, V <sub>GE</sub> = –15/+15 V, I <sub>C</sub> = 75 A                                                     | –    | 340   | –    | nC   |
| R <sub>thJH</sub>                                                                                 | Thermal Resistance – chip–to–heatsink | Thermal grease, Thickness = 2.1 Mil ±2%<br>λ = 2.9 W/mK                                                                         | –    | 0.66  | –    | K/W  |
| R <sub>thJC</sub>                                                                                 | Thermal Resistance – chip–to–case     |                                                                                                                                 | –    | 0.48  | –    | K/W  |
| IGBT INVERSE DIODE (D11, D21, D12, D22, D13, D23) AND BYPASS DIODE (D51, D61, D52, D62, D53, D63) |                                       |                                                                                                                                 |      |       |      |      |
| V <sub>F</sub>                                                                                    | Diode Forward Voltage                 | I <sub>F</sub> = 30 A, T <sub>J</sub> = 25°C                                                                                    | –    | 1.04  | 1.7  | V    |
|                                                                                                   |                                       | I <sub>F</sub> = 30 A, T <sub>J</sub> = 150°C                                                                                   | –    | 0.94  | –    |      |
| R <sub>thJH</sub>                                                                                 | Thermal Resistance – chip–to–heatsink | Thermal grease, Thickness = 2.1 Mil ±2%<br>λ = 2.9 W/mK                                                                         | –    | 1.04  | –    | K/W  |
| BOOST SILICON CARBIDE SCHOTTKY DIODE (D31, D41, D32, D42, D33, D43)                               |                                       |                                                                                                                                 |      |       |      |      |
| I <sub>R</sub>                                                                                    | Diode Reverse Leakage Current         | V <sub>R</sub> = 1200 V, T <sub>J</sub> = 25°C                                                                                  | –    | –     | 600  | μA   |
| V <sub>F</sub>                                                                                    | Diode Forward Voltage                 | I <sub>F</sub> = 30 A, T <sub>J</sub> = 25°C                                                                                    | –    | 1.42  | 1.7  | V    |
|                                                                                                   |                                       | I <sub>F</sub> = 30 A, T <sub>J</sub> = 150°C                                                                                   | –    | 1.85  | –    |      |
| t <sub>rr</sub>                                                                                   | Reverse Recovery Time                 | T <sub>J</sub> = 25°C<br>V <sub>DS</sub> = 600 V, I <sub>C</sub> = 50 A<br>V <sub>GE</sub> = –9 V, 15 V, R <sub>G</sub> = 1 Ω   | –    | 15    | –    | ns   |
| Q <sub>rr</sub>                                                                                   | Reverse Recovery Charge               |                                                                                                                                 | –    | 128   | –    | nC   |
| I <sub>RRM</sub>                                                                                  | Peak Reverse Recovery Current         |                                                                                                                                 | –    | 13    | –    | A    |
| di/dt                                                                                             | Peak Rate of Fall of Recovery Current |                                                                                                                                 | –    | 4200  | –    | A/μs |
| E <sub>rr</sub>                                                                                   | Reverse Recovery Energy               |                                                                                                                                 | –    | 16    | –    | μJ   |

# NXH300B100H4Q2F2, NXH300B100H4Q2F2SG-R

## ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25°C unless otherwise noted) (continued)

| Symbol                                                                     | Parameter                             | Test Condition                                                                                                                 | Min | Typ  | Max | Unit |
|----------------------------------------------------------------------------|---------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|-----|------|-----|------|
| <b>BOOST SILICON CARBIDE SCHOTTKY DIODE (D31, D41, D32, D42, D33, D43)</b> |                                       |                                                                                                                                |     |      |     |      |
| t <sub>rr</sub>                                                            | Reverse Recovery Time                 | T <sub>J</sub> = 125°C<br>V <sub>DS</sub> = 600 V, I <sub>C</sub> = 50 A<br>V <sub>GE</sub> = -9 V, 15 V, R <sub>G</sub> = 1 Ω | —   | 19   | —   | ns   |
| Q <sub>rr</sub>                                                            | Reverse Recovery Charge               |                                                                                                                                | —   | 175  | —   | nC   |
| I <sub>RRM</sub>                                                           | Peak Reverse Recovery Current         |                                                                                                                                | —   | 17   | —   | A    |
| di/dt                                                                      | Peak Rate of Fall of Recovery Current |                                                                                                                                | —   | 3153 | —   | A/μs |
| E <sub>rr</sub>                                                            | Reverse Recovery Energy               |                                                                                                                                | —   | 18   | —   | μJ   |
| R <sub>thJH</sub>                                                          | Thermal Resistance – chip-to-heatsink | Thermal grease, Thickness = 2.1 Mil ±2%<br>λ = 2.9 W/mK                                                                        | —   | 0.85 | —   | K/W  |
| R <sub>thJC</sub>                                                          | Thermal Resistance – chip-to-case     |                                                                                                                                | —   | 0.73 | —   | K/W  |

## THERMISTOR CHARACTERISTICS

|                  |                            |                           |    |      |   |      |
|------------------|----------------------------|---------------------------|----|------|---|------|
| R <sub>25</sub>  | Nominal resistance         |                           | —  | 22   | — | kΩ   |
| R <sub>100</sub> | Nominal resistance         | T = 100°C                 | —  | 1486 | — | Ω    |
| ΔR/R             | Deviation of R25           |                           | -5 | —    | 5 | %    |
| P <sub>D</sub>   | Power dissipation          |                           | —  | 200  | — | mW   |
|                  | Power dissipation constant |                           | —  | 2    | — | mW/K |
|                  | B-value                    | B (25/50), tolerance ±3%  | —  | 3950 | — | K    |
|                  | B-value                    | B (25/100), tolerance ±3% | —  | 3998 | — | K    |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

# NXH300B100H4Q2F2, NXH300B100H4Q2F2SG-R

## TYPICAL CHARACTERISTICS – IGBT, INVERSE & BYPASS DIODE AND BOOST DIODE




Figure 2. Typical Output Characteristics




Figure 3. Typical Output Characteristics




Figure 4. Transfer Characteristics




Figure 5. Typical Saturation Voltage Characteristics




Figure 6. Inverse Diode Forward Characteristics




Figure 7. Boost Diode Forward Characteristics

TYPICAL CHARACTERISTICS – IGBT, INVERSE & BYPASS DIODE AND BOOST DIODE (CONTINUED)




Figure 8. Typical Turn On Loss vs.  $I_C$




Figure 9. Typical Turn Off Loss vs.  $I_C$




Figure 10. Typical Turn On Loss vs.  $R_g$




Figure 11. Typical Turn Off Loss vs.  $R_g$




Figure 12. Typical Reverse Recovery Energy Loss vs.  $I_C$




Figure 13. Typical Reverse Recovery Energy Loss vs.  $R_g$

TYPICAL CHARACTERISTICS – IGBT, INVERSE & BYPASS DIODE AND BOOST DIODE (CONTINUED)




Figure 14. Typical Turn-Off Switching Time vs.  $I_c$




Figure 15. Typical Turn-On Switching Time vs.  $I_c$




Figure 16. Typical Turn-Off Switching Time vs.  $R_g$




Figure 17. Typical Turn-On Switching Time vs.  $R_g$




Figure 18. Typical Reverse Recovery Time vs.  $R_g$




Figure 19. Typical Reverse Recovery Charge vs.  $R_g$

TYPICAL CHARACTERISTICS – IGBT, INVERSE & BYPASS DIODE AND BOOST DIODE (CONTINUED)




Figure 20. Typical Reverse Recovery Peak Current vs.  $R_g$




Figure 21. Typical di/dt vs.  $R_g$




Figure 22. Typical Reverse Recovery Time vs.  $I_C$




Figure 23. Typical Reverse Recovery Charge vs.  $I_C$




Figure 24. Typical Reverse Recovery Current vs.  $I_C$




Figure 25. FBSOA

# NXH300B100H4Q2F2, NXH300B100H4Q2F2SG-R

## TYPICAL CHARACTERISTICS – IGBT, INVERSE & BYPASS DIODE AND BOOST DIODE (CONTINUED)




Figure 26. RBSOA




Figure 27. Capacitance Charge




Figure 28. Gate Voltage vs. Gate Charge




Figure 29. NTC Characteristics

TYPICAL CHARACTERISTICS – IGBT, INVERSE & BYPASS DIODE AND BOOST DIODE (CONTINUED)




Figure 30. Transient Thermal Impedance (IGBT)




Figure 31. Transient Thermal Impedance (BOOST DIODE)




Figure 32. Transient Thermal Impedance (INVERSE&BYPASS DIODE)


## NXH300B100H4Q2F2, NXH300B100H4Q2F2SG-R

### ORDERING INFORMATION

| Orderable Part Number                                      | Marking                                     | Package                                                                       | Shipping                |
|------------------------------------------------------------|---------------------------------------------|-------------------------------------------------------------------------------|-------------------------|
| NXH300B100H4Q2F2PG<br>PRESS FIT PINS                       | NXH300B100H4Q2F2PG                          | Q2BOOST – PIM53, 93x47 (PRESSFIT)<br>(Pb-Free and Halide-Free Press Fit Pins) | 12 Units / Blister Tray |
| NXH300B100H4Q2F2SG,<br>NXH300B100H4Q2F2SG-R<br>SOLDER PINS | NXH300B100H4Q2F2SG,<br>NXH300B100H4Q2F2SG-R | Q2BOOST – PIM53, 93x47 (SOLDER PIN)<br>(Pb-Free and Halide-Free Solder Pins)  | 12 Units / Blister Tray |

PIM53, 93x47 (PRESSFIT)  
CASE 180CB  
ISSUE O


DATE 30 APR 2020



NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009
2. CONTROLLING DIMENSION : MILLIMETERS
3. DIMENSIONS b AND b1 APPLY TO THE PLATED TERMINALS AND ARE MEASURED AT DIMENSION A1
4. PIN POSITION TOLERANCE IS  $\pm 0.4\text{mm}$
5. PACKAGE MARKING IS LOCATED AS SHOWN ON THE SIDE OPPOSITE THE PACKAGE ORIENTATION FEATURES

GENERIC  
MARKING DIAGRAM\*



XXXXX = Specific Device Code  
G = Pb-Free Package  
AT = Assembly & Test Site Code  
YYWW= Year and Work Week Code

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

| DIM | MILLIMETERS |        |        |
|-----|-------------|--------|--------|
|     | MIN.        | NOM.   | MAX.   |
| A   | 16.90       | 17.30  | 17.70  |
| A1  | 13.97       | 14.18  | 14.39  |
| A2  | 11.70       | 12.00  | 12.30  |
| A3  | 4.40        | 4.70   | 5.00   |
| A4  | 16.40       | 16.70  | 17.00  |
| b   | 1.61        | 1.66   | 1.71   |
| b1  | 0.75        | 0.80   | 0.85   |
| D   | 92.90       | 93.00  | 93.10  |
| D1  | 104.45      | 104.75 | 105.05 |
| D2  | 81.80       | 82.00  | 82.20  |
| D3  | 106.90      | 107.20 | 107.50 |
| E   | 46.70       | 47.00  | 47.30  |
| E1  | 44.10       | 44.40  | 44.70  |
| E2  | 38.80       | 39.00  | 39.20  |
| P   | 5.40        | 5.50   | 5.60   |
| P1  | 10.60       | 10.70  | 10.80  |
| P2  | 1.80        | 2.00   | 2.20   |

NOTE 4

| PIN | PIN POSITION |       | PIN | PIN POSITION |       |
|-----|--------------|-------|-----|--------------|-------|
|     | X            | Y     |     | X            | Y     |
| 1   | 70.50        | 2.60  | 29  | 50.70        | 36.50 |
| 2   | 70.50        | 0.00  | 30  | 50.70        | 33.50 |
| 3   | 64.25        | 0.00  | 31  | 54.00        | 36.50 |
| 4   | 61.65        | 0.00  | 32  | 56.60        | 36.50 |
| 5   | 40.35        | 0.00  | 33  | 67.90        | 36.50 |
| 6   | 37.75        | 0.00  | 34  | 70.50        | 36.50 |
| 7   | 31.50        | 0.00  | 36  | 70.50        | 22.35 |
| 8   | 28.90        | 0.00  | 37  | 70.50        | 19.75 |
| 9   | 8.85         | 0.00  | 38  | 50.95        | 19.15 |
| 10  | 6.25         | 0.00  | 39  | 56.85        | 17.05 |
| 11  | 0.00         | 0.00  | 41  | 53.85        | 16.55 |
| 12  | 0.00         | 2.60  | 42  | 61.00        | 6.70  |
| 13  | 0.00         | 6.75  | 43  | 58.40        | 5.35  |
| 14  | 0.00         | 9.75  | 44  | 32.65        | 27.80 |
| 15  | 0.00         | 12.75 | 45  | 33.35        | 25.20 |
| 17  | 0.00         | 33.50 | 47  | 26.35        | 18.65 |
| 18  | 0.00         | 36.50 | 48  | 25.35        | 15.65 |
| 19  | 3.30         | 36.50 | 50  | 39.00        | 16.55 |
| 20  | 5.90         | 36.50 | 51  | 44.90        | 19.15 |
| 21  | 19.80        | 36.50 | 52  | 42.00        | 16.55 |
| 22  | 19.80        | 33.90 | 53  | 34.70        | 10.55 |
| 23  | 25.35        | 36.50 | 54  | 34.70        | 7.95  |
| 24  | 25.35        | 33.90 | 55  | 12.60        | 27.65 |
| 25  | 39.25        | 36.50 | 56  | 11.60        | 25.05 |
| 26  | 41.85        | 36.50 | 58  | 10.85        | 10.30 |
| 27  | 45.15        | 36.50 | 59  | 10.85        | 7.70  |
| 28  | 45.15        | 33.50 |     |              |       |

DOCUMENT NUMBER: 98AON20720H

DESCRIPTION: PIM53 93X47 (PRESS FIT)



Electronic versions are uncontrolled except when accessed directly from the Document Repository.  
Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

PIM53, 93x47 (SOLDER PIN)  
CASE 180CC  
ISSUE O

DATE 04 MAY 2020



| DIM | MILLIMETERS |        |        |
|-----|-------------|--------|--------|
|     | MIN.        | NOM.   | MAX.   |
| A   | 16.80       | 17.20  | 17.60  |
| A2  | 11.70       | 12.00  | 12.30  |
| A3  | 4.40        | 4.70   | 5.00   |
| A4  | 16.40       | 16.70  | 17.00  |
| b   | 0.95        | 1.00   | 1.05   |
| D   | 92.90       | 93.00  | 93.10  |
| D1  | 104.45      | 104.75 | 105.05 |
| D2  | 81.80       | 82.00  | 82.20  |
| D3  | 106.90      | 107.20 | 107.50 |
| E   | 46.70       | 47.00  | 47.30  |
| E1  | 44.10       | 44.40  | 44.70  |
| E2  | 38.80       | 39.00  | 39.20  |
| P   | 5.40        | 5.50   | 5.60   |
| P1  | 10.60       | 10.70  | 10.80  |
| P2  | 1.80        | 2.00   | 2.20   |


NOTE 4

| PIN | PIN POSITION |       | PIN | PIN POSITION |       |
|-----|--------------|-------|-----|--------------|-------|
|     | X            | Y     |     | X            | Y     |
| 1   | 70.50        | 2.60  | 29  | 50.70        | 36.50 |
| 2   | 70.50        | 0.00  | 30  | 50.70        | 33.50 |
| 3   | 64.25        | 0.00  | 31  | 54.00        | 36.50 |
| 4   | 61.65        | 0.00  | 32  | 56.60        | 36.50 |
| 5   | 40.35        | 0.00  | 33  | 67.90        | 36.50 |
| 6   | 37.75        | 0.00  | 34  | 70.50        | 36.50 |
| 7   | 31.50        | 0.00  | 36  | 70.50        | 22.35 |
| 8   | 28.90        | 0.00  | 37  | 70.50        | 19.75 |
| 9   | 8.85         | 0.00  | 38  | 50.95        | 19.15 |
| 10  | 6.25         | 0.00  | 39  | 56.85        | 17.05 |
| 11  | 0.00         | 0.00  | 41  | 53.85        | 16.55 |
| 12  | 0.00         | 2.60  | 42  | 61.00        | 6.70  |
| 13  | 0.00         | 6.75  | 43  | 58.40        | 5.35  |
| 14  | 0.00         | 9.75  | 44  | 32.65        | 27.80 |
| 15  | 0.00         | 12.75 | 45  | 33.35        | 25.20 |
| 17  | 0.00         | 33.50 | 47  | 26.35        | 18.65 |
| 18  | 0.00         | 36.50 | 48  | 25.35        | 15.65 |
| 19  | 3.30         | 36.50 | 50  | 39.00        | 16.55 |
| 20  | 5.90         | 36.50 | 51  | 44.90        | 19.15 |
| 21  | 19.80        | 36.50 | 52  | 42.00        | 16.55 |
| 22  | 19.80        | 33.90 | 53  | 34.70        | 10.55 |
| 23  | 25.35        | 36.50 | 54  | 34.70        | 7.95  |
| 24  | 25.35        | 33.90 | 55  | 12.60        | 27.65 |
| 25  | 39.25        | 36.50 | 56  | 11.60        | 25.05 |
| 26  | 41.85        | 36.50 | 58  | 10.85        | 10.30 |
| 27  | 45.15        | 36.50 | 59  | 10.85        | 7.70  |
| 28  | 45.15        | 33.50 |     |              |       |

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009
2. CONTROLLING DIMENSION : MILLIMETERS
3. DIMENSIONS b AND b1 APPLY TO THE PLATED TERMINALS AND ARE MEASURED AT DIMENSION A1
4. PIN POSITION TOLERANCE IS  $\pm 0.4\text{mm}$
5. PACKAGE MARKING IS LOCATED AS SHOWN ON THE SIDE OPPOSITE THE PACKAGE ORIENTATION FEATURES

GENERIC  
MARKING DIAGRAM\*



XXXXX = Specific Device Code  
G = Pb-Free Package  
AT = Assembly & Test Site Code  
YYWW = Year and Work Week Code

\*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

|                  |                          |                                                                                                                                                                                     |
|------------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| DOCUMENT NUMBER: | 98AON20721H              | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION:     | PIM53 93X47 (SOLDER PIN) | PAGE 1 OF 1                                                                                                                                                                         |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)

