


DRAWING MADE IN AMERICAN PROJECTION



LTR	REVISION RECORD	ECN	DR	CHK	DATE
D1	ECO-09-022178		KK	AEG	SEP09

NUMBER

C-160783



FOR 2.0 (079) 3M PIN



3 OBSOLETE PARTS: OBSOLETE CIS
STREAMLINING PER D.RENAUD/D.SINISI

1 FOR USE ON MINIATURE APPLICATORS;
LEFT - RIGHT FEED
2 FOR USE ON MINIATURE APPLICATORS;
AMP-O-MATOR APPLICATION ; LEFT-RIGHT FEED

160783-8	3	NICKEL-SILVER	NONE	Δ
160783-6		PH BRONZE	PRE-TINNED	Δ
160783-5		STEEL	PRE-NICKEL	Δ
160783-4		PH BRONZE	NONE	Δ
160783-3	3	PH BRONZE	PRE-TINNED	Δ

CUSTOMER COPY FOR REFERENCE ONLY

© 1978 BY AMP-HOLLAND N.V. ALL RIGHTS
RESERVED AMP PRODUCTS COVERED BY
PATENTS AND OR PATENTS PENDING.



AMP-HOLLAND N.V.
's-Hertogenbosch

WIRE RANGE	INSUL. RANGE	FIRST USED
0.2 - 0.8 mm 0.08 - 0.31 in.	0.2 - 0.8 mm 0.08 - 0.31 in.	

SCALE	SIZE	NO
1:1	A	

C-160783

REV
D1

ORDER NO	MATERIAL	PLATING

DATE	DATE	DATE	DATE
21.12.78			

DATE	DATE	DATE	DATE
21.12.78			

RECEPTACLE FOR 2.0 (079) 3M PIN

AMP 1202-M

DIMENSIONS IN MM DO NOT SCALE PRINT