

US-EMLP (22X22) - Plastic label



0828796
<https://www.phoenixcontact.com/us/products/0828796>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plastic label, Card, white, unmarked, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, THERMOMARK PRIME, THERMOMARK CARD 2.0, THERMOMARK CARD, THERMOMARK PRIME 2.0, mounting type: adhesive, Number of individual labels: 24, text field height: 22 mm, text field width: 22 mm

Your advantages

- The markers, which are supplied as uniform cards, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The US-EMLP ... UniSheet labeling range includes self-adhesive device markers with good adhesive properties
- The perforated markers and labels are easy to separate and can be easily fitted
- The sheets provide space for including function texts
- PVC material flammability rating V0 in accordance with UL 94

Commercial data

Item number	0828796
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG09
Product key	BG2419
GTIN	4046356558860
Weight per piece (including packing)	18.22 g
Weight per piece (excluding packing)	18.22 g
Customs tariff number	39199080
Country of origin	DE

US-EMLP (22X22) - Plastic label



0828796

<https://www.phoenixcontact.com/us/products/0828796>

Technical data

Product properties

Marking

Number of individual labels	24
Number of individual labels per row	4
Identification technology	Thermal transfer for sheets and cards, UV LED technology

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

RoHS compliant	yes
Foil strength	500 µm
Adhesive strength	50 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Material	PVC
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 80 °C
Ambient temperature (storage/transport)	10 °C ... 30 °C
Permissible humidity (storage/transport)	40 % ... 70 %
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Dimensions

Width	21.8 mm
Height	21.8 mm
Depth	0.55 mm

Text field

Text field width	22 mm
Text field height	22 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

US-EMLP (22X22) - Plastic label



0828796

<https://www.phoenixcontact.com/us/products/0828796>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/0828796>



CSA

Approval ID: 70191766

US-EMLP (22X22) - Plastic label



0828796

<https://www.phoenixcontact.com/us/products/0828796>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

US-EMLP (22X22) - Plastic label



0828796
<https://www.phoenixcontact.com/us/products/0828796>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com