







LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
CM	00		0	REVISED PER 0638-0087-04	07MAY04	KW	SR	
			01	REVISED PER ECO-05-001793	27MAY05	KW	SR	
			02	REVISED PER ECO-09-025699	11DEC09	KK	AEG	
			A	REVISED PER ECR-21-118133	22OCT2021	SS	VS	




1. PARTS COMPLY TO AMP SOLDERABILITY SPECIFICATION 109-11-3.
2. CIRCUIT IDENTIFICATION CHARACTERS ARE ADJACENT TO THE INDICATED CAVITIES, BUT LOCATION AND ORIENTATION MAY DIFFER FROM PRINT.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.
4. IDENTIFICATION WILL APPEAR AT CIRCUIT NO. 1, OTHERS OPTIONAL.
5. CONTACT IS PLATED WITH 0.00127 [0.00050] NICKEL, THEN 0.000075 [0.00030] GOLD OVER CONTACT LENGTH INDICATED AND MATTE TIN ON SOLDER TAIL END.
6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
7. DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY CONDITION. ADDITIONAL 2% GROWTH DUE TO END USE LOCATION MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.



SCALE 4:1



6	OBSOLETE	PHOSPOR BRONZE, GOLD 5	NYLON, UL94V-2,NATURAL	1586134-2
		PHOSPOR BRONZE, PRE-TIN	NYLON, UL94V-2,NATURAL	1586134-1
		PIN CONTACT MATERIAL AND FINISH	HOUSING MATERIAL AND COLOR	PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE WITHOUT NOTICE. ANY MODIFICATION TO THIS DRAWING SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN K. WHITAKER 07MAY04	Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK S. RIDGILL 07MAY04	NAME S. RIDGILL 07MAY04 PIN HEADER ASSEMBLY, 5 CIRCUIT, NO DRAIN HOLES, UNIVERSAL MATE-N-LOK™		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC			
0 PLC ±		APPLICATION SPEC			
1 PLC ±		WEIGHT			
2 PLC ±0.13(.005)		SIZE			
3 PLC ±		CAGE CODE			
4 PLC ±		DRAWING NO			
ANGLES ±0°30'		RESTRICTED TO			
FINISH		A			
MATERIAL SEE TABLE		00779 C=1586134			
SEE TABLE		CUSTOMER DRAWING			
		SCALE 5:1 SHEET 1 OF 1 REV A			