






	1	2	3	4	5	6	7	
A	Material Item 1 Clamp:Brass,Ni plated Item 2 Terminal screw: Steel Zinc plating "-" slot type Item 3 Wire guard solder pin: Brass,Tin plated Item 4 Insulator (housing): Thermoplastic(UL94V-0),Blue Electrical UL / VDE Voltage rating: 300V/250V Current rating: 15A/10A Wire range: 0.34-4.0mm² Solid wire(AWG): 12-24 Stranded wire(AWG): 12-24 Torque(Lb-In): 3.5 Lb-In / 0.4 N.m Screw: M2.5 Wire strip length: 6-7mm Withstanding Voltage: 1.6KV/2KV Operating temperature: -40°C to +115°C Soldering temperature: 250°C±10°C/5 Sec Safety Approval:  							A
B								B
C								C
D								D
E								E
F								F
G								G
H								H



RECOMMENDED PCB LAYOUT

N=Number of poles
A=Nx5.0
B=(N-1)x5.0

TOL

POLES	A	B
2p-6p	±0.15	±0.15
7p-12p	±0.20	±0.20
13p-18p	±0.30	±0.30
19p-24p	±0.40	±0.40

RoHS compliant

Unit: mm

3



File No.: E349947

Scale	1:1						Date	Name	Customer-No.
TOLERANCE						Drawn	25.10.2007	Hellwig	
X.	±0.50					Approved	18.04.2016	Joanna	ASSMANN WSW-No.
X.X	±0.30								A-TB500-TGxx
X.XX	±0.10	3	Add UL	18.04.2016	Joanna				Drawing-No.
DIM	TOL	2	Update	21.04.2010	Dean				
X.°	±1°								
		1	Drawn	25.10.2007	Hellwig				
Angle	TOL	Id.	Modification	Date	Name				