


NOTES:
1. MATERIAL AND FINISH:
 BODY - STAINLESS STEEL, PASSIVATED
 CONTACT PIN - BERYLLIUM COPPER, GOLD PLATING
 INSULATOR - ULTEM, NATURAL


2. ELECTRICAL:
 A. IMPEDANCE: 50 OHM
 B. FREQUENCY RANGE: DC - 40 GHz
 C. VSWR: 1.25 MAX.
 D. INSERTION LOSS: 0.05XSQRT(F(F IN GHz)
 E. DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS, MIN.

3. ENVIRONMENTAL:
 A. TEMPERATURE RANGE: - 40 °C to +85 °C
 B. DURABILITY: 500 CYCLES

REVISIONS				
REV	DESCRIPTION	DATE	ECN	BY
A	RELEASE TO MFG	11-Dec-25	17692	LEO



SCALE 3.500



CUSTOMER OUTLINE DRAWING
ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

NOTICE: These drawings, specifications, or other data (1) are, and remain the property of Amphenol corp. (2) must be returned upon request; and (3) are confidential and not to be disclosed to any person other than those to whom they are given by Amphenol Corp. The furnishing of these drawings, specifications, or other data by Amphenol Corp., or to any other person to anyone for any purpose is not to be regarded by implication or otherwise in any manner licensing, granting rights to permitting such holder or any other person to manufacture, use or sell any product, process or design, patented or otherwise, that may in any way be related to or disclosed by said drawings, specifications, or other data.				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE METRIC (INCHES) AND TOLERANCES ARE: <0.5mm = ±0.05mm [$<0.020 = \pm 0.002$] 0.5 - 6mm = ±0.1mm [$>0.020 - 0.236 = \pm 0.004$] >6.00 - 30mm = ±0.2mm [$>0.236 - 1.181 = \pm 0.008$] >30.00 - 120mm = ±0.3mm [$>1.181 - 4.725 = \pm 0.012$]				MATERIAL SEE NOTES		TITLE 2.4MM JACK TO 2.4MM JACK ADAPTER		Amphenol RF									
												B		SIZE		DRAWING NO. 24MM7071A1-SXPE130G-50		REV A			
														ITEM NO. 467071AAAA1ZU5F							
														PART NO. AD-24J24J-1							
THIRD ANGLE PROJ. 				REFERENCE EAR# 10272				ANGLES = ±1°				ENGR.1 STAMN		ENGR.2 P.SALOMAO		DATE 11-Dec-25		SHEET NO. 2 OF 2		SCALE: 12.0:1.0	