

Copper braid

Copper braid for EMC-compliant screening protects the cable from interferences transmitted by other electrical fields, also for the automotive industry (ISO-TS approved).



Interference signals



Temperature-resistant

Application range

EMC-compliant screening
Can be used as earthing tape
Automotive industry

Included

Are delivered in 2 pieces with 50 m each

Design

Variable diameter by tightening the braid

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001182
ETIM 5.0 Class-Description: Braided hose

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001182
ETIM 6.0 Class-Description: Braided hose

General:

Minor differences are possible depending on the production batch

Note:

Degree of coverage: 85 % at maximum opening

Material:

Tinned-copper

Temperature range:

-30 °C to +105 °C
Max. temperature: +120 °C (short-term)

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (02.12.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Copper braid

Article number	Article designation	mm ²	Diameter in mm	Number of wires x Ø (mm)	Copper index (kg/km)	PU (m)
61721370	CU 14	1.32	1 - 4	24 x 7 x 0,1	13.2	100
61721380	CU 410	4.14	4 - 10	24 x 22 x 0,1	41.4	100
61721390	CU 1020	8.29	10 - 20	48 x 22 x 0,1	81.9	100
61721395	CU 2050	18.1	20 - 50	48 x 12 x 0,2	183	100

Last Update (02.12.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16