



Desktop 3D printer G150 (150*150*150mm)

SKU 114991766



Product Feature: The G150 3D Desktop Printer is our most popular 3D printers where it can be used for personal interest projects all the way to prototypes for commercial projects by providing an easy to use and reliable prototyping experience.

- 1 +

CN Warehouse

Estimated availability Date: Jun 07, 2019



Pre Order

Tags:

3D Printers

Manufacturing Equipment

Prototyping

Description

Documents

Learn

Reviews

FAQS

If you would like to purchase or obtain more information about this item, please email us at: Manufacturing@chailuo.org

• The G150 3D Desktop Printer is our most popular 3D printers where it can be used for personal interest projects all the way to prototypes for commercial projects by providing an easy to use and reliable prototyping experience.

• G150 also facilitates with Cura, the open-source 3D printing software, allowing 3D models to be printed out using 3D printers with ease. On top of that, Cura has built a large [user community](#) which are very useful for frontend support.

Product Features:

- **Moulding Method:** FDM
- **Software Language:** English/Chinese
- **LCD Screen:** Full Colour Touch Screen
- **Printing Precision(mm):** 0.05-0.2
- **Moulding Size(mm):** 150*150*150
- **Layer Thickness(mm):** 0.05-0.2
- **Nozzle Temperature:** 0-235°C
- **Moving Speed:** 200-500mm/s
- **Positioning Precision(mm):** X/Y axis: 11μ; Z axis: 2.5μ
- **Build Plate Temperature:** Professional build plates do not require heating
- **Filaments:** PLA/ABS
- **Input Voltage/Frequency/Current/Power:** 220V, 50-60HZ, 5.4A/2.2A, 350W
- **Filament Diameter(mm):** 1.75
- **Interface Type:** USB/SD Card
- **Frame:** Metal
- **Operator Interface:** LCD
- **File Format:** STL/OBJ
- **Environment: Temperature:** 15-32°C, Humidity 20-50%
- **Quality Certificates:** CE,FCC,ROHS

TECHNICAL PARAMETERS

| | |
|--|------------------------------------|
| Moulding Method | FDM |
| Software Language | English/Chinese |
| LCD Screen | Full colour touch screen |
| Printing Precision(mm) | 0.05-0.2 |
| Moulding Size(mm) | 150*150*150mm |
| Layer Thickness(mm) | 0.05-0.2 |
| Nozzle Temperature | 0-235°C |
| Move Speed | 200-500mm/s |
| Positioning Precelsion(mm) | X/Y axis 11μ; Z axis 2.5μ |
| Build Plate Temperature | Professional plate without heating |
| Packing size | 760x305x315 mm |
| Filaments | PLA/ABS |
| Filament Diameter(mm) | 1.75 |
| Input Voltage/Frequency/Currency/Power | 220V, 50-60HZ, 5.4A/2.2A, 350W |

| | |
|-------------------------|--------------------------|
| Interface Type | USB/SD Card |
| Frame | Metal |
| Operator Interface | LCD |
| File Format | STL/OBJ |
| Environment Temperature | 15-32°C, Humidity 20-50% |
| Quality Certificates | CE,FCC,ROHS |

Company

About Seed
Distributors
Careers
Contacts

Help Center

How to Get Help
FAQ
Technical Support
Shipping & Order
Warranty & Returns
Payment Information

Community

Project Hub
Forum
Blog
Wiki

Stay Tuned

>

