

Product data sheet

Specifications



APC Smart-UPS On-Line, 8kVA/
8kW, Tower, 230V 3:1 and 1:1, 6x
C13+4x C19 IEC outlets, Network
Card+SmartSlot, Extended runtime,
W/O rail kit

SRT8KXLI

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead time	Usually in Stock

Main

Main Input Voltage	230 V 400 V 3 phases
Product or component type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V 380 V 415 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	8000 W
Rated power in VA	8000 VA
output connection type	6 IEC 60320 C13 3 IEC Jumpers 4 IEC 60320 C19
Output connector type	Hard wire 3-wire (H N + E) 1
Provided equipment	CD with software Documentation CD Installation guide Temperature probe USB cable Warranty card Web/SNMP management card
Range of product	Smart-UPS On-Line

Batteries & Runtime

Run Time	View Runtime Graph 
Efficiency	View Efficiency Graph 
Battery type	Lead-acid battery
Battery voltage	+/- 192 V (split battery referenced to neutral)
Extended runtime	1
Number of battery filled slots	0
Battery recharge time	1.5 h

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of battery replacement quantity	2
Battery life	3...5 year(s)
Replacement battery	APCRBC140 
Battery charger power	876 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	High density
Redundant	No
UPS type	Double conversion online

Physical

Colour	Black
Height	432 mm
Width	263 mm
Depth	715 mm
Net weight	111.82 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Rack-mounted with kit
Two post mountable	0
USB compatible	Yes

Input

Input voltage limits	100...275 V adjustable (half load) 173...476 V adjustable (half load)
Number of input connectors	1 hard wire 3-wire (1P + N + E) 1 hard wire 5-wire (3P + N + E)
Network frequency	40...70 Hz auto-sensing

Output

Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1
Harmonic distortion	Less than 2 %
Maximum configurable power in VA	8000 VA
Maximum configurable power in W	8000 W
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	CE EAC IRAM RCM VDE
Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	55 dBA
Heat dissipation	1497 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0...15240 m
IP degree of protection	IP20
Relative humidity	0...95 % non-condensing
Storage Relative Humidity	0...95 % non-condensing

Communications & Management

Emergency power off	Yes
Free slots	1
Preinstalled device	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity

Surge Protection and Filtering

Surge energy rate	480 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	46.1 cm
Package 1 Width	60 cm
Package 1 Length	100 cm
Package 1 Weight	126.82 kg

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	17644
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	409c68a1-39a6-4e5f-b080-12befe783ad8
REACH Regulation	REACH Declaration

Energy efficiency	
Energy Efficiency Optimized	Energy efficient product

Use Again

Repack and remanufacture	
End of life manual availability	End of Life Information
Removable battery	User replaceable
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Image of product / Alternate images

Alternative



