

J1MSWD - 5XM Product Details

Share

Print

Email



Military/Aerospace High Performance Relays

[Not EU RoHS or ELV Compliant](#)

Product Highlights:

- ? 1MSD TO -5 Relay Series
- ? Input Voltage = 5 VDC
- ? Contact Arrangement = 1 Form C, SPDT, 1 C/O
- ? Contact - Rated Current = 1 A
- ? Non Polarized, Monostable Coil - Magnetic System

[View all Features](#)

Quick Links

- ? [Check Pricing & Availability](#)
- ? [Search for Tooling](#)
- ? [Product Feature Selector](#)
- ? [Contact Us About This Product](#)

J1MSWD - 5XM

(1-1617120 -3)

TE Internal Number: 1 - 1617120 - 3

Active

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

Documentation & Additional Information	
Product Drawings: ? None Available Catalog Pages/Data Sheets: ? RELAY (PDF, English) Product Specifications: ? None Available Application Specifications: ? None Available Instruction Sheets: ? None Available CAD Files: ? None Available	Additional Information: ? Product Line Information Related Products: ? Tooling
List all Documents	

Product Features (Please use the Product Drawing for all design activity)	
Product Type Features: ? Series = 1MSD TO -5 Relay ? Termination Type = Long Leads Electrical Characteristics: ? Input Voltage (VDC) = 5 ? Contact - Rated Current (A) = 1 ? Coil Polarity Protection Diode = Without ? Transistor Driver = Without ? Coil Resistance (?) = 125 ? MOSFET Driver = Without ? Coil Power Measurement = Milliwatts ? Coil - Rated Power (mW) = 200 ? Actuating System = DC ? Shock = 75 G's, 6ms ? Vibration = 30G's, 10 to 3000Hz Contact Features: ? Mounting Options = PC Board ? Enclosure Type = Hermetically Sealed	Configuration Features: ? Contact Arrangement = 1 Form C, SPDT, 1 C/O ? Coil - Magnetic System = Non Polarized, Monostable ? Coil Suppression Diode = With Industry Standards: ? Government/Industry Qualification = Yes ? Government/Industry Part Number = M39016/25 -017M ? RoHS/ELV Compliance = Not ELV/RoHS compliant ? Lead Free Solder Processes = Not suitable for lead free processing ? Approved Standards = M39016 Qualified, M Level Conditions for Usage: ? Temperature Range (°C) = -65 - +125 Other: ? Brand = CII

Corporate Information

Who We Are

Investors

News Room

Supplier Portal

Careers

Quick Links

Check Distributor Inventory

Cross Reference

Find Documents & Drawings

Product Compliance Support Center

Site Map

Customer Support

Email or Chat With Us

Find a Phone Number

Search Knowledge Base

Manage your Account

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

