

COAXIAL ADAPTER, MFBX, 50 Ohm, plug / plug (male / male)
32_MFBX-50-0-1/111_N

Properties

- High axial float
- Price/Performance optimized
- Blind mateable
- Reliable and secure connection



Product configuration		
Interface type	Gender	Standard
MFBX	plug (male)	HUBER+SUHNER MFBX
MFBX	plug (male)	HUBER+SUHNER MFBX

Interface and material data		
MFBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE / LCP	
MFBX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Bronze	SUCOPRO Plating
Insulator	PFA / PTFE / LCP	

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data	
Weight	0.00076 kg
Mating cycles	50

Environmental data	
Operation temperature	-55 °C ... 155 °C

COAXIAL ADAPTER, MFBX, 50 Ohm, plug / plug (male / male)
32_MFBX-50-0-1/111_N

Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
85025361	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
85008489	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
85095759	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c

Ordering Information Table			
Item number	Item description	Packaging type	Packaging information
85025361	32_MFBX-50-0-1/111_NE	Single	
85008489	32_MFBX-50-0-1/111_NH		
85095759	32_MFBX-50-0-1/111_NH-2	Bulk 100 pcs	Huaawei Specific

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2329 / Date of publication: 12.07.2025 / uncontrolled copy