



SODIMM

M471A5244CB0-CWE



Overview

Specifications

Related resources

Related insights

Proven DRAM module solution in the global market

Samsung’s memory modules are designed for a wide range of applications to deliver the best performance with low power requirements.

Specifications

DDR	DDR4	Dimm Type	SODIMM
Density	4 GB	Rank x Org.	1R x 16
Speed	3200 Mbps	Voltage	1.2 V
No. of Pin	260	Component Composition	(512M x 16) x 4
Product Status	Mass Production		

SEE ALL

Related resources



Handling guide

Related insights



EUV: The Quiet Revolution in DRAM Speaks Volumes for the

Samsung's leadership in EUV technology paves the way for the memory industry to take a leap forward.

[LEARN MORE >](#)



How Samsung Memory Is Fueling the Evolution of Automotive

Samsung is providing powerful automotive memory solutions that are empowering the development of more sophisticated autonomous driving, in-vehicle infotainment and connectivity.

[LEARN MORE >](#)



All product specifications reflect internal test results and are subject to variations by user's system configuration. All product images shown are for illustration purposes only and may not be an exact representation of the product. Samsung reserves the right to change product images and specifications at any time without notice.

Newsroom

[Product finder](#)

[Technical resources](#)

[TCO calculator](#)

[About us](#)

PRODUCTS

[DRAM](#)

[SSD](#)

[eSTORAGE](#)

[MCP](#)

[PROCESSOR](#)

SOLUTIONS

[APPLICATIONS](#)

[TOPICS](#)

[TECHNOLOGY](#)

Other Sites

[中文\(简体\)](#)

[B2B Workplace](#)

[Memory \(日本語\)](#)

[ISOCELL](#)

[Exynos](#)

Follow us




IMAGE SENSOR

SECURITY
SOLUTIONS

DISPLAY IC

POWER IC

LED 

Display 

Worker Safety 

Samsung Business 

Copyright © 1995-2020 SAMSUNG All Rights Reserved.

PRIVACY

LEGAL

SITEMAP

This website is best viewed using Microsoft Internet Explorer 9 or higher, and/or latest version of Google Chrome and Mozilla Firefox browsers.