


DWG. NO.

SYM	DCN NO.	DESCRIPTION	DATE	DRAWN	CHECKED	APP' D	APP' D



DESCRIPTION	APPLICABLE WIRE		AWG# MARK
	WIRE SIZE	OUTER DIA. OF INSUL.	
D02-22-22P-10000	AWG#22~24	^{DIA} 1.3 MAX.	22
D02-22-26P-10000	AWG#26~28	^{DIA} 1.1 MAX.	26


NOTE 1. CONTACT TO BE SUPPLIED IN REELED FORM.

(10,000 CONTACT/REEL)

2. NUMBER OF CONTACTS TO BE SHOWN ON THIS PORTION.

3. LABEL SHOWING PART NUMBER & Q'TY TO BE PUT ON THIS PORTION.

DIMENSIONS ARE IN MILLIMETERS	
TOLERANCES ON: (INCHES)	
<u>DIMENSION</u>	<u>ANGLES</u>
. ± 0.3	X° ±
.X ± 0.3	X°X' ±
.XX ±	
.XXX ±	
	<u>CONCENTRICITY</u>
	WITHIN T, J, R.



3	PIN CONTACT	10000	COPPER ALLOY	GOLD OVER NICKEL	
2	PAPER TAPE	1	PAPER		
1	MAGAZINE	1	PAPER		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARKS
REFERENCE DOCUMENT JACS-3050-2		DATE 9 JUN. '87	SCALE 10/1	JAE-CONNECTOR.COM Reference Only	
MATERIAL	DRAWN E. MURANO		TITLE D02-22-22P-10000 D02-22-26P-10000		
	CHECKED Y. HAYASHI				
	APP'D <i>K. Takeuchi</i>				
TREATMENT	APP'D <i>S. Ishimoto</i>		SERIES	DWG. NO. SJ021507-E	

CS P-5150

SIZE A3