





APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	2/10/10	
A		REVISED SPEC.	5/15/13	
B		UPDATED DRAWING	3/15/17	HR/CH



SECTION A-A



SECTION B-B



SPECIFICATIONS:

Material: Phosphor Bronze, 0.2mm thick

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250 VAC

Current rating: 3 A

Contact resistance: 20 mohms max

Mechanical:

Wire Range: 22-28 AWG.

Packaging: 10K Pcs / Reel

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN DY 2/10/10

CHECKED

APPROVED

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

.098 [2.50] CRIMP TERMINAL

SIZE

X

PART NO.

25CTE-R

REV.

B

REF: S00123T

SCALE: NTS

SHEET 1 OF 1