

FLORENCE-O

~85° + 35° oval beam

SPECIFICATION:

Dimensions	61.0 x 286.0
Height	8.5 mm
Fastening	screw
ROHS compliant	yes ⓘ


MATERIALS:

Component	Type	Material	Colour	Finish	Length (mm)
FLORENCE-O	Linear lens	PMMA	clear		



ORDERING INFORMATION:

Component	Qty in box	MOQ	MPQ	Box weight (kg)
F15069_FLORENCE-O » Box size: 398 x 298 x 140 mm	72	18	6	7.5





See also our general installation guide: www.ledil.com/installation_guide

OPTICAL RESULTS (MEASURED):





LED LUXEON XR-3535L (L202 - xxxx033C30001)
 FWHM / FWTM 93.0 + 45.0° / 133.0 + 113.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED NFSW757H
 FWHM / FWTM 88.0 + 48.0° / 130.0 + 120.0°
 Efficiency 93 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Duris E5
 FWHM / FWTM 91.0 + 46.0° / 131.0 + 115.0°
 Efficiency 92 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS


LED Fortimo LED Line VO 1ft MF 3R HV5
 FWHM / FWTM 92.0 + 45.0° / 132.0 + 115.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS



LED Fortimo LED Line 1ft 650lm 3R HV4 & LV4
 FWHM / FWTM 92.0 + 46.0° / 132.0 + 116.0°
 Efficiency 94 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

PHILIPS

LED Fortimo LED Line 1ft HF 3R HV5
 FWHM / FWTM 91.0 + 48.0° / 132.0 + 121.0°
 Efficiency 93 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

PHILIPS



LED	Fortimo LED Line 1ft LF 3R HV5 & LV5
FWHM / FWTM	92.0 + 46.0° / 132.0 + 117.0°
Efficiency	94 %
Peak intensity	0.7 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

PHILIPS


LED	Fortimo LED Line 1ft MF 3R HV5 & LV5
FWHM / FWTM	91.0 + 48.0° / 133.0 + 119.0°
Efficiency	94 %
Peak intensity	0.6 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

SAMSUNG

LED	LM28xB Series
FWHM / FWTM	92.0 + 46.0° / 131.0 + 112.0°
Efficiency	87 %
Peak intensity	0.6 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (MEASURED):





LED SEOUL 3030
FWHM / FWTM 91.0 + 47.0° / 131.0 + 116.0°
Efficiency 92 %
Peak intensity 0.6 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files





LED SEOUL 5630C
FWHM / FWTM 92.0 + 44.0° / 132.0 + 111.0°
Efficiency 92 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



LED SEOUL DC 3030
FWHM / FWTM 93.0 + 44.0° / 132.0 + 116.0°
Efficiency 94 %
Peak intensity 0.7 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:





Light distribution files

OPTICAL RESULTS (MEASURED):

TRIDONIC

LED	LLE G2 55x280mm 2000lm
FWHM / FWTM	91.0 + 46.0° / 132.0 + 114.0°
Efficiency	94 %
Peak intensity	0.7 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED J Series 5050 Round LES
 FWHM / FWTM 87.0 + 51.0° / 129.0 + 113.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files




LED LUXEON 5050 Round LES
 FWHM / FWTM 88.0 + 51.0° / 126.0 + 109.0°
 Efficiency 90 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED LUXEON 5050 Square LES
 FWHM / FWTM 90.0 + 55.0° / 128.0 + 115.0°
 Efficiency 90 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):




LED NFSx757G
 FWHM / FWTM 83.0 + 35.0° / 122.0 + 86.0°
 Efficiency 94 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 2
 Light colour/type White
 Required components:



Light distribution files




LED NVSxE21A
 FWHM / FWTM 93.0 + 28.0° / 121.0 + 71.0°
 Efficiency 92 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files



LED Duris S5 (Single chip)
 FWHM / FWTM 90.0 + 32.0° / 125.0 + 82.0°
 Efficiency 92 %
 Peak intensity 0.9 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

OSRAM
Opto Semiconductors


LED Duris S5 (Single chip)
FWHM / FWTM 82.0 + 34.0° / 120.0 + 84.0°
Efficiency 92 %
Peak intensity 0.9 cd/lm
LEDs/each optic 2
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors


LED Duris S8
FWHM / FWTM 90.0 + 63.0° / 132.0 + 125.0°
Efficiency 92 %
Peak intensity 0.5 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

OSRAM
Opto Semiconductors

LED OSCONIQ C 2424
FWHM / FWTM 92.0 + 33.0° / 124.0 + 73.0°
Efficiency 95 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED LM301B
 FWHM / FWTM 86.0 + 56.0° / 128.0 + 119.0°
 Efficiency 92 %
 Peak intensity 0.6 cd/lm
 LEDs/each optic 2
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG


LED LM301B
 FWHM / FWTM 90.0 + 35.0° / 126.0 + 87.0°
 Efficiency 94 %
 Peak intensity 0.8 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:



Light distribution files

SAMSUNG

LED LM301D
 FWHM / FWTM 90.0 + 40.0° / 126.0 + 92.0°
 Efficiency 90 %
 Peak intensity 0.7 cd/lm
 LEDs/each optic 1
 Light colour/type White
 Required components:




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED	LM302B
FWHM / FWTM	90.0 + 33.0° / 124.0 + 79.0°
Efficiency	92 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

SAMSUNG


LED	LM302Z plus
FWHM / FWTM	78.0 + 37.0° / 117.0 + 91.0°
Efficiency	93 %
Peak intensity	0.9 cd/lm
LEDs/each optic	2
Light colour/type	White
Required components:	



Light distribution files

SAMSUNG

LED	LM561B Plus
FWHM / FWTM	90.0 + 37.0° / 126.0 + 95.0°
Efficiency	91 %
Peak intensity	0.8 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	




Light distribution files

OPTICAL RESULTS (SIMULATED):

SAMSUNG


LED	LM561C
FWHM / FWTM	90.0 + 35.0° / 125.0 + 84.0°
Efficiency	94 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files




LED	SEOUL 5630D
FWHM / FWTM	87.0 + 37.0° / 126.0 + 90.0°
Efficiency	89 %
Peak intensity	0.8 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files



LED	SEOUL DC 3030C
FWHM / FWTM	92.0 + 36.0° / 128.0 + 87.0°
Efficiency	94 %
Peak intensity	0.9 cd/lm
LEDs/each optic	1
Light colour/type	White
Required components:	



Light distribution files

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDiL Oy

Joensuunkatu 7
FI-24100 SALO
Finland

LEDiL Inc.

228 West Page Street
Suite D
Sycamore IL 60178
USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B
Casic Motor Building
Shenzhen 518057
P.R.CHINA

Local sales and technical support

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)

Shipping locations

Poznan, Poland
Hong Kong, China

Distribution Partners

[www.ledil.com/
where_to_buy](http://www.ledil.com/where_to_buy)